







Recommended P.C.B Layout(Top Side)
(PCB BOARD TOLERANCE±0.05)




SPECIFICATIONS
Rated Current:3.0AMP
Contact Resistance:20mΩ Max
Withstand Voltage:1000V AC/DC
Insulation Resistance:1000MΩ Min
Operation Temperature:-40°c to +105°c


Contact Material:Brass
Contact Plating:Au or Sn Over Ni
Insulator Material:Polyester(UL94V-0)
Standard: PA6T
Max.Processing Temp: 230°C for 30-60 seconds
(260°C for 10 seconds)



P = With Post



默认 = W/O Post



special cap for 2*2pin

Ordering Information

PM 254	- *	- N	- S	- *	- **	- *	- P
No. of Rows 1=Single Row 2=Dual Row	No. of Pins 2-40Pin	Type Z=直插 H=带焊 S=全贴 P=带插	Length (Plastic) (图高)	Contact G0:Gold Flash G1:1u" Gold G2:3u" Gold G3:5u" Gold G4:10u" Gold G5:15u" Gold G6:30u" Gold S0:Gold Flash/Tin S1:tin	Plating	Packing R=Reel +Cap (编带+盖)	Post (带柱)

			GENERAL TOLERANCE		制 图 DRAWING	深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO.,LTD			
			DIM	TOL	审 核 CHECK				
			X. X	±0.30	批 准 APPROVAL	产品名称 TITLE	2.54双排 排母 贴片 编带+盖 (塑高7.1)	版 本 REV.	A
			X. XX	±0.20	比 例 SCALE	产品料号 PART NO.	PM254-2-N-S-7.1-XX-R(L7.5)	单 位 UNITS	mm
			X. XXX	±0.10	投 影 Projection	材 料 MATERIAL		页 次 SHEET	1/1
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE	Angle	±3.0°					