



SPECIFICATIONS  
 Rated Current:3.0AMP  
 Contact Resistance:20m ΩMax  
 Withstand Voltage:1000V AC/DC  
 Insulation Resistance:1000M ΩMin  
 Operation Temperature:-40°C to +105°C

Contact Material:Brass  
 Contact Plating:Au or Sn Over Ni  
 Insulator Material:Polyester(UL94V-0)  
 Resistance To Soldering Heat:  
 245°C±5°C, 10s(PBT insulator)  
 260°C±5°C, 10s(PA6T&PA9T&LCP insulator)

**Ordering Information**

HC-NJ 254 - \* - N - \* - \* - \* - \*

No. of Rows 2= Dual Row	No. of Pins 6-64Pin	Type 1= (111) 2= (112) 3= (113)	Length (mm) (01.00)	Contact 00= Gold 01= 1u" Gold 02= 3u" Gold 03= 5u" Gold 04= 10u" Gold 05= 15u" Gold 06= 30u" Gold S0= Gold Flash/Tin S1= Tin	Plating Flash	Color B= Black G= Grey	Latch Type L= Long Latch S= Short Latch N= Without Latch
----------------------------	------------------------	--	---------------------------	---	------------------	------------------------------	---

			GENERAL TOLERANCE		制图 DRAWING		深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO., LTD			
			DIM	TOL	审核 CHECK					
			X. X	±0.30	批准 APPROVAL		产品名称 TITLE	2.54 牛角 弯针 (长耳扣)	版本 REV.	A
			X. XX	±0.20	比例 SCALE		产品料号 PART NO.	HC-NJ254-2-N-W-27.8-XX-X-L	单位 UNITS	mm
			X. XXX	±0.10	投影 Projection		材料 MATERIAL		页次 SHEET	1/1
			Angle	±3.0°						
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE								