








Recommended P.C.B Layout(Top Side)
(PCB BOARD TOLERANCE±0.05)



P = With Post



默认= W/O Post

SPECIFICATIONS

Rated Current:1.0AMP
Contact Resistance:20mΩ Max
Withstand Voltage:500V AC/DC
Insulation Resistance:1000MΩ Min
Operation Temperature:-40°C to +105°C

Contact Material:Brass
Contact Plating:Au or Sn Over Ni
Insulator Material:Polyester(UL94V-0)
Standard: PA6T
Max.Processing Temp: 230°C for 30-60 seconds
(260°C for 10 seconds)

Pitch	塑高变量 (mm)
1.27mm	0.85
	1.0
	1.5
	1.7
	2.0
	2.5

Dimension antitheses list

ITEM	PA	PB	W	L
Standard	4.00	1.50	5.50	5.50

Ordering Information

PZ 127 - * - N - * - * - ** - * - P

No. of Rows
1=Single Row
2=Dual Row

No. of Pins
2=20Pin
N=50Pin

Type
N=单针
S=双针
N/S=混合

Length
(mm)

Contact Plating
G0:Gold Flash
G1:1u" Gold
G2:3u" Gold
G3:5u" Gold
G4:10u" Gold
G5:15u" Gold
G6:30u" Gold
S0:Gold Flash/Tin
S1:Tin

Packing
R=Reel
+Cap (编带+盖)

Post
(带柱)

			GENERAL TOLERANCE		制 图	深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO., LTD			
			DIM	TOL	DRAWING				
			X. X	±0.30	审 核	产品名称	1.27 双排 排针 贴片 编带+盖	版本	A
			X. XX	±0.20	CHECK	TITLE	(塑高1.0)	REV.	
			X. XXX	±0.10	批 准	产品料号	PZ127-2-N-S-1.0-XX-R(L5.5)	单 位	mm
			Angle	±3.0°	APPROVAL	PART NO.		UNITS	
序号	变更内容	日期			比 例	材 料		页 次	1/1
No.	MODIFY CONTENT	MODIFY DATE			SCALE	MATERIAL		SHEET	
					投影				
					Projection				