


Recommended P.C.B Layout(Top Side)
(PCB BOARD TOLERANCE ± 0.05)



SPECIFICATIONS

Rated Current:3.0AMP

Contact Resistance:20mΩ Max

Withstand Voltage:1000V AC/DC

Insulation Resistance:1000MΩ Min

Operation Temperature: -40°C to +105°C




Contact Material:Brass

Contact Plating: Au Over Ni

Insulator Material: Polyester (UL94V-0)

Standard: PA6T

Max.Processing Temp: 230°C for 30–60 seconds
(260°C for 10 seconds)



Dimension antitheses list				
ITEM	PA	A	PC	L
Standard	6.00	3.94	8.50	17.00
Alternate				

Ordering Information

PZ 254	- *	- N	- WS	- *	- **	- R
	└─┬─┘	└─┬─┘	└─┬─┘	└─┬─┘	└─┬─┘	└─┬─┘
No. of Rows 1=Single Row 2=Dual Row	No. of Pins 2-40Pin	Type (240Pin) (90Pin) (2-40Pin)	Length (产品长度)	Contact G0:Gold	Plating Flash Gold	Packing R=Reel (箱)+Cap (封箱)+Cap
				G1:1u" Gold	G2:3u" Gold	
				G3:5u" Gold	G4:10u" Gold	
				G5:15u" Gold	G6:30u" Gold	
				30:Gold Flash/Tin	S1:tin	

			GENERAL TOLERANCE		制 图 DRAWING	 深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO.,LTD			
			DIM	TOL	审 核 CHECK				
			X. X	±0.30	批 准 APPROVAL	产品名称 TITLE	2.54 双排 卧贴 排针 编带+盖 (塑高2.5)	版 本 REV.	A
1	初版发行		X. XX	±0.20	比 例 SCALE	产品料号 PART NO.	PZ254-2-N-WS-2.5-XX-R (L17.0)	单 位 UNITS	mm
			X. XXX	±0.10		投 影 Projection		材 料 MATERIAL	页 次 SHEET
序号 No.	变更内容 MODIFY CONTENT	日 期 MODIFY DATE	Angle	±3.0°					


深圳市华灿天禄电子有限公司
 ShenzhenhuacantianluELECTRONICS CO.,LTD

产品名称 TITLE	2.54 双排 卧贴 排针 编带+盖 (塑高2.5)	版 本 REV.	A
---------------	-------------------------------	-------------	---

产品料号 PART NO.	PZ254-2-N-WS-2.5-XX-R(L17.0)	单位 UNITS	mm
------------------	------------------------------	-------------	----

材 料 MATERIAL		页 次 SHEET	1/1
-----------------	--	--------------	-----