




Engineer Drawing



3D VIEW





NOTES:

- 1.HUOSING: LCP HIGH-TEMP THERMOPLASTIC UL94V-0 COLOR:BEIGE
- 2.TERMINAL:PHOSPHOR BRONZE

IPCB 08 471 MXX X X X

① ② ③ ④ ⑤ ⑥ ⑦ ⑧

- ① Series Type
- ② Pitch:0.8mm
- ③ Height
- ④ Connector Type
- ⑤ Pin Code:See Table 1
- ⑥ Rows Code
- ⑦ Serial Code
- ⑧ Other Code



RECOMMENDED P.C.BOARD LAYOUT

Table 1

Pin Code	NO.of contacts	Dimensions					
		A	B	C	D	E	F
20	20	13.80	7.20	8.80	12.20	10.86	12.21
30	30	17.80	11.20	12.80	16.20	14.86	16.21
40	40	21.80	15.20	16.80	20.20	18.86	20.21
50	50	25.80	19.20	20.80	24.20	22.86	24.21
60	60	29.80	23.20	24.80	28.20	26.86	28.21
80	80	37.80	31.20	32.80	36.20	34.86	36.21
A0	100	45.80	39.20	40.80	44.20	42.86	44.21
C0	120	53.80	47.20	48.80	52.20	50.86	52.21
E0	140	61.80	55.20	46.80	60.20	58.86	60.21
G0	160	69.80	63.20	64.80	68.20	66.86	68.21
I0	180	77.80	71.20	72.80	76.20	74.86	76.21
K0	200	85.80	79.20	80.80	84.20	82.86	84.21

TOLERANCES:

X.=±0.25
X.X=±0.20
X.XX=±0.10
GENERAL ANGLE
X°=±1°

NCP

www.i-ncp.com

PART NO:
IPCB08471M xxS7V

NAME:
0.8PH H4.7 BTB Male
Receptacle Assembly H5.0

DRAWING NO
IPCB08471M07V

SHEET 1 OF 1

UNITS:mm SCALE:1:1 REV.03