







Recommended P.C.B Layout(Top Side)
(PCB BOARD TOLERANCE±0.05)




SPECIFICATIONS

Rated Current:1.5AMP
Contact Resistance:20mΩMax
Withstand Voltage:500V AC/DC
Insulation Resistance:1000MΩMin
Operation Temperature:-40°C to +105°C

Contact Material:Brass
Contact Plating:Au or Sn Over Ni
Insulator Material:Polyester(UL94V-0)
Standard: PA6T
Max.Processing Temp: 230°C for 30-60 seconds
(260°C for 5-10 seconds)



P=With Post



默认=W/O Post

Ordering Information

PM 200	- *	- N	- S	- *	- **	- *	- P
No. of Rows 1=Single Row 2=Dual Row	No. of Pins 2-40Pin	Type Z=直针 R=弯针 S=立贴 W=带贴	Length (塑料) G0:1u" Gold G1:1u" Gold G2:3u" Gold G3:5u" Gold G4:10u" Gold G5:15u" Gold G6:30u" Gold S0:Gold Flash/Tin S1:Tin	Contact Plating	R=Reel +Cap (带卷)	Post (带柱)	

			GENERAL TOLERANCE	制 图 DRAWING	深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO.,LTD			
			DIM TOL	审 核 CHECK				
			X. X ±0.30	批 准 APPROVAL	产品名称 TITLE	2.00双排 排母 贴片 编带+盖 (塑高6.35)	版本 REV.	A
1	初版发行		X. XX ±0.20	比 例 SCALE	产品料号 PART NO.	PM200-2-N-S-6.35-XX-R (L6.95)	单 位 UNITS	mm
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE	X. XXX ±0.10	投 影 Projection	材 料 MATERIAL		页 次 SHEET	1/1
			Angle ±3.0°					