





- 1.Material:
 - 1.1 Housing: PBT UL94V-0 Black.
 - 1.2 Contact :Phosphor Bronze,Gold plated on contact area 30u”.
 - 1.3 Input Terminal : Brass.
 - 1.4 Metal shielding:Copper alloy with Nickel plated.
- 2.Environmental requirements:
 - 2.1 Lead-free process,compliant RoHS.

RJ45-418-052-XX

类别码
05:6.73规格

MANUFACTURE DWG		 东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co.,Ltd			
UNLESS OTHERWISE SPECIFIED TOLERANCES			TITLE: RJ45立式有壳左黄右绿DIP B3.89 100%30u" PBT		
			PAR	RJ45-418-052-02	
DECIMALS:	ANGLES:		DWN	Lucas	
.X:±0.35	X":±3"		CHKD	Ethan	
.XX:±0.25	X.X":±2"	APVD	Jacob		
.XXX:±0.15	X.XX":±1"	SCALE:1:1	UNIT:MM		
		CUSTOMER COPY	SIZE:A4	SHEET:1F1	
				REV:A	



3. Electrical Specification @25°C:

3.1 Inductance: 350uH Min With 8mA DC bias.

3.2 Insertion loss :
1-100MHZ -1dB max.

3.3 Return loss :
1-30MHZ -18dB min.
30-60MHZ -16dB min.
60-80MHZ -12dB min.

3.4 Common Mode Rejection: 1-100MHZ -30dB min.

3.5 Cross Talk: 1-100MHZ -30dB min.

4. Operating and Storage Temperature:

4.1 Operating Temperature : 0°C to +70°C.

4.2 Storage Temperature : -40°C to +85°C.

5. Wave soldering peak temperature: 260°C.

Emitting Color	λ_p (nm)	$V_f @ I_f = 20\text{mA}$
Green	565	1.8-2.5V
Yellow	585	1.8-2.5V

MANUFACTURE DWG		 东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co., Ltd.	
		TITLE: RJ45 立式有壳左黄右绿 DIP B3.89 100% 30u" PBT	
		PAR	RJ45-418-052-02
		DWN	Lucas
		CHKD	Ethan
		APVD	Jacob
DECIMALS:	ANGLES:	SCALE 1:1	UNIT: MM
.X: ±0.35	X.*: ±3°	SIZE: A4	SHEET: 1F1
.XX: ±0.25	X.X*: ±2°	CUSTOMER COPY	REV: A
.XXX: ±0.15	X.XX*: ±1°		