

D

C



B

A

C

B

A



1. WILL ACCEPT (20) MULTIMATE AND 2 TYPE XII PIN CONTACTS.	9 TE LOGO AND PART NUMBER LOCATED ON ANY FLANGE EDGE	OBSOLETE	8 4	Ø3.81±0.08(.125±.003) HOLES	YES	A	1-206613-2
			4	#4-40 THREADED INSERTS	NO	A	1-206613-0
		OBSOLETE	7	Ø3.81±0.08(.125±.003) HOLES	YES	A	206613-9
		PRELIMINARY	6 4	Ø3.81±0.08(.125±.003) HOLES	YES	A	206613-7
		OBSOLETE	4	#4-40 THREADED INSERTS	NO	A	206613-6
2. CAVITY IDENTIFICATION ON FRONT AND REAR FACE.			4	Ø3.81±0.08(.125±.003) HOLES	YES	A	206613-5
			4	Ø3.81±0.08(.125±.003) HOLES	NO	B	206613-3
			4	Ø3.81±0.08(.125±.003) HOLES	NO	A	206613-1
		NOTES	MOUNTING FEATURE	PERIPHERAL SEAL	SEE DETAIL	PART NUMBER	
3 NUMBER 4 FASTENERS RECOMMENDED FOR MOUNTING.		THIS DRAWING IS A CONTROLLED DOCUMENT.					
		DIMENSIONS: mm (INCHES)	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± 0.13 (.005) 3 PLC ± - 4 PLC ± - ANGLES ± -	DWN M. BINNER05/26/94 CHK R. STONE6-23-94 APVD - NAME			
				PRODUCT SPEC 108-10024			
		MATERIAL	FINISH	APPLICATION SPEC			
				WEIGHT - SIZE A1 CASE CODE 00779 DRAWING NO C=206613 RESTRICTED TO -			
		CUSTOMER DRAWING SCALE 2:1 SHEET 1 OF 1 REV U					
4 HOUSING: NYLON, BLACK. PERIPHERAL SEAL: ELASTOMER, BLACK.		STE TE Connectivity					
		RECEPTACLE HOUSING, STANDARD SEX, SHELL SIZE 23, CPC					
		-					
		-					
		-					
5 APPLIES TO 206613-6 ONLY.		-					
		-					
		-					
		-					
		-					
6 PERMANENT WHITE MARKED OR WHITE INK STAMPED CAVITY INDENTIFICATION.		-					
		-					
		-					
		-					
		-					
7 HOUSING: NYLON, RED. PERIPHERAL SEAL: ELASTOMER, BLACK.		-					
		-					
		-					
		-					
		-					
8 WHITE DOT NEAR POSITION 1 ON WIRE ENTRY FACE.		-					
		-					
		-					
		-					
		-					