








NOTES

- 1 - CORROSION RESISTANT STEEL ENCLOSURE
- 2 - SWITCH SEALED PER MIL-PRF-8805 SYMBOL 4
- 3 - COINCIDENCE OF OPERATING AND RELEASING POINTS:
.010 OF PLUNGER TRAVEL
- 4 - CIRCUIT DIAGRAM, CATALOG LISTING AND DATE CODE
ARE SHOWN ON NAMEPLATE
- 5 - HARDWARE MAY BE PACKAGED UNASSEMBLED PER MIL-PRF-8805
- 6 - REPLACEMENT MOUNTING HARDWARE PACKET: 198PA78-EN

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH

THIRD ANGLE PROJECTION



CHARACTERISTICS

OPERATING FORCE -----	6-12 LB
FULL OVERTRAVEL FORCE -----	30 LB MAX
RELEASE FORCE -----	4 LB MIN
PRETRAVEL -----	.040 MAX
DIFFERENTIAL TRAVEL -----	.020 MAX
OVERTRAVEL -----	.250 MIN
FREE POSITION	

ELECTRICAL DATA

CONTACT ARRANGEMENT 2X S P D T		
LOAD	28 VDC	
	SEA LEVEL	50,000 FT.
RES	4	4
IND	2	2
MOTOR	4	

SCALE	FULL
-------	------

DO NOT SCALE PRINT		
UNLESS OTHERWISE SPECIFIED TOLERANCES ARE		
ONE PLACE	(.0)	±
TWO PLACE	(.00)	±
THREE PLACE	(.000)	±
ANGLES		±
WEIGHT	14.5 OZ MAX	

ANSI Y14.5M-1982 APPLIES