

CAP OPTIONS	TOGGLE SWITCHES	TACTILE SWITCHES	SNAP ACTION SWITCHES	SLIDE SWITCHES	ROTARY SWITCHES	ROCKER SWITCHES	PUSHBUTTON SWITCHES	NAVIGATION SWITCHES	KEYLOCK SWITCHES	DIP SWITCHES	DETECTOR SWITCHES	ANTI-VANDAL SWITCHES
----------------	--------------------	---------------------	-------------------------	-------------------	--------------------	--------------------	------------------------	------------------------	---------------------	-----------------	----------------------	-------------------------



FEATURES & BENEFITS

- 25mm diameter panel cutout
- LED color options
- Dot, ring or power symbol illumination available
- Multiple function options
- IP65 rated
- SPDT & DPDT arrangements
- Soldered wire leads (300mm long) optional

Series	Actuator Options	Terminal Options	Function Options	Rating Options	Body Finish Options	Actuator Finish Options	Lens Style Options	LED-Color Options	Illumination Voltage Options	Graphic (Optional)
	F - Flat	2 - Solder W - Wire Leads 300mm long	T - 1 Pole 1P Off-(On) + 1P On-(Off) Y - 1 Pole 1P Off-(On) + 1P On-(Off) U - 2 Pole 2P Off-(On) + 2P On-(Off) V - 2 Pole 2P Off-(On) + 2P On-(Off)	0 - 2A, 48VDC	1 - Black Anodized N - Nickel Plated S - Stainless Steel	1 - Black Anodized N - Nickel Plated S - Stainless Steel	NONE - Non-Illuminated 2 - Dot Illumination 3 - Ring Illumination	NONE - Non-Illuminated 0 - White 1 - Red 2 - Orange 3 - Green 4 - Blue 5 - Yellow	NONE - Non-Illuminated 1 - Base Voltage 3 - 6V 4 - 12V 5 - 24V 6 - 125V 7 - 250V	M11 - Power symbol laser etched M14 - Power symbol / Ring Illumination

NOTES:
 *() denotes function is momentary

Specifications subject to change without notice 3.15.2022





E♦SWITCH®

800.867.2717

1


STANDARD LED FUNCTIONS T & U




SPDT - FUNCTION T
TERMINALS 1a - 4a

DPDT - FUNCTION U
TERMINALS 1a - 4a AND
1b - 4b (AS SHOWN)


TERMINALS (-) AND (+)
USED WITH ILLUMINATED
OPTION ONLY




SPDT LED SCHEMATIC





SPDT Non ILL SCHEMATIC



DPDT LED SCHEMATIC





DPDT Non ILL SCHEMATIC



PV8 SERIES ANTI-VANDAL SWITCH


STANDARD LED FUNCTIONS Y & V




SPDT - FUNCTION Y
TERMINALS 1a - 4a

DPDT - FUNCTION V
TERMINALS 1a - 4a AND
1b - 4b (AS SHOWN)


TERMINALS (-) AND (+)
USED WITH ILLUMINATED
OPTION ONLY




SPDT LED SCHEMATIC




SPDT Non ILL SCHEMATIC




DPDT LED SCHEMATIC



DPDT Non ILL SCHEMATIC



PANEL CUTOUT



POWER SYMBOL PANEL CUTOUT



E-SWITCH®


www.e-switch.com

800.867.2717


3

PV8 SERIES ANTI-VANDAL SWITCH


ACTUATOR OPTIONS



FLAT NON-ILLUMINATED






FLAT DOT ILLUMINATED




FLAT RING ILLUMINATED

GRAPHIC OPTIONS



M11



M14



E-SWITCH®

www.e-switch.com

800.867.2717

4

ANTI-VANDAL SWITCHES
DETECTOR SWITCHES
DIP SWITCHES
KEYLOCK SWITCHES
NAVIGATION SWITCHES
PUSHBUTTON SWITCHES
ROCKER SWITCHES
ROTARY SWITCHES
SLIDE SWITCHES
SNAP ACTION SWITCHES
TACTILE SWITCHES
TOGGLE SWITCHES
CAP OPTIONS

PV8 SERIES ANTI-VANDAL SWITCH

STANDARD LED WIRE LEAD

SWITCH	WIRE	LENGTH
SW1-1a	WIRE, 24AWG AWM UL1015, WHITE	300.0 [11.8 in]
SW1-2a	WIRE, 24AWG AWM UL1015, WHITE	300.0 [11.8 in]
SW1-3a	WIRE, 24AWG AWM UL1015, BLUE	300.0 [11.8 in]
SW1-4a	WIRE, 24AWG AWM UL1015, BLUE	300.0 [11.8 in]
SW1-1b	WIRE, 24AWG AWM UL1015, WHITE	300.0 [11.8 in]
SW1-2b	WIRE, 24AWG AWM UL1015, WHITE	300.0 [11.8 in]
SW1-3b	WIRE, 24AWG AWM UL1015, BLUE	300.0 [11.8 in]
SW1-4b	WIRE, 24AWG AWM UL1015, BLUE	300.0 [11.8 in]
SW1- (+)	WIRE, 24AWG AWM UL1015, RED	300.0 [11.8 in]
SW1- (-)	WIRE, 24AWG AWM UL1015, BLACK	300.0 [11.8 in]

** WIRE LEADS PROVIDED ARE DEPENDANT ON THE FUNCTION AND/OR ILLUMINATION SELECTED **

