






PC Board Layout
Ref.

RoHS Compliant



DWG NO. MJF13T3L-KF06B3YG-0808

CHECKED BY CY

TOLERANCES ARE

FILE NO.

DRAWING BY

 $\bar{X} \pm 0.2$

.XX ± 0.1

$$.XXX \pm$$

AWG

DESCRIPTION:

1: SINGLE PORT, RJ45, SHIELDED, WITH LED
WITH TRANSFORMER, SIDE ENTRY PCB JACK

AREA

REVISIONS

HK

DATE

煜倫股份有限公司

TRANSFORMER TYPE 3


Specification :

Item	Parameter	Condition	Min.	Typ.	Max.	Unit	REMARK
1	Insertion loss	1-100 MHz			-1	dB	
2	Return loss	1-30 MHz	-16			dB	NOTE 1
		30-60 MHz				dB	
		60-80 MHz	-10			dB	
3	DCL	100 KHz	350			μ H	
4	Crosstalk	1-100 MHz	-35			dB	
5	Hipot	Vrms	1.5			kV	
6	Turns Ratio (Chip : Cable)	TX: 1 : 1 RX: 1 : 1				CT	
7	Direct Current resistance					Ω	

*NOTE 1: Greater than $(16-20 \text{ Log } (f/30\text{MHz}))$ dB.

CONNECTOR SOLDER SIDE

RJ45
CONTACT SIDE



CONNECTOR SCHEMATIC

MORETHANALL
CONNECTORS
ASSEMBLIES

PART NO. MJF13T3L-KF06B3YG-0808

DWG NO. MJF13T3L-KF06B3YG-0808

CHECKED BY CY

FILE NO.

DRAWING BY

TOLERANCES ARE

.X $\pm$ 0.2
.XX $\pm$ 0.1
.XXX $\pm$
AWG

DESCRIPTION:

TRANSFORMER TYPE 3
SPECIFICATION

煜倫股份有限公司

UNIT / mm

SCALE 1:1

PROJECTION



AREA

REVISIONS

HK

DATE