








REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	C200275	2020-03-13	Nan_Su	△B*1




Recommended PCB Layout

Conn.
Pin Assignments
Front ViewRecommended
Panel Cut-Out

Note:

- * ⌀ Important Dimension To Check.
- * Waterproof Rating: IP67(Mated Waterproof)
- * Connector: PBT+PC, Black
- * Male Pins: Copper Alloy, Gold Plated
- * Shell: Zinc Alloy, Nickel Plated
- * Nut: Zinc Alloy, Nickel Plated
- * Grounding Pin: Copper Alloy, Tin Plated
- * O-Ring1: Silicone, Black
- * O-Ring2: Silicone, Gray
- * Pin Holder: PBT+PC, Black
- * For Panel Thickness Max. 3.0mm
- * For PCB Thickness Max. 1.6mm



UNIT:mm		
TOLERANCE	.X	±0.25
	.XX	±0.1
	.XXX	±0.05
ANGLES		±1°

TITLE M12,90° Panel,w/ Grounding Pin 5PIN MCONN MPIN (Mated Waterproof)			
SCALE 3:2	SIZE A4	SHEET 1 OF 1	
REV. B	WC-REV. A.1	⌀ Inspection item	

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO MSBS-05PMMR-SF7003	DRAWN BY Yulong_wang	DATE 2016-12-11
DWG NO MSBS-05PMMR-SF7003	CHECKED BY Jinhai	DATE 2016-12-11
CUSTOMER ALTW	APPROVED BY Jerry	DATE 2016-12-11