



Rating: 1A 30V DC  
 Contact Resistance: 50 mΩ Max.  
 Operating temperature: -25°C ~ 80°C  
 Operating force: 3~30N  
 Operating Life: 5,000cycles

②	Shunt terminal	6	COPPER ALLOY	Plating Au		
①	Housing	1	PA9T	Black		
ITEM	PART NAME	Serial number	QTY.	MATERIAL	FINISHING	REMARK
APPROVALS		DATE		hro®		
DRAWN	LIUCAN	2023.4.13		TITLE:	PHONE JACKES	
APPROVALS				PART NO.	PJ-332F	
TOLERANCES ARE		30~以上	±0.30	ANGLE	UNIT: mm	SCALE: 1:1
		10~30	±0.20			PROJ:
		5~10	±0.15	±2°	DRAWING NO.	
		~ 5	±0.10		SHEET	1 OF 1

—	A	—	NEW	—	—	—
ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.