


| PART NO. | "A" REF.    | "B"±.016<br>(±0.41) | INTERCHANGE<br>WITH SCANBE |
|----------|-------------|---------------------|----------------------------|
| RSDC-250 | 2.5 (63.5)  | 1.5 (38.1)          | 11633-1                    |
| RSDC-300 | 3.0 (76.2)  | 2.0 (50.8)          |                            |
| RSDC-350 | 3.5 (88.9)  | 2.5 (63.5)          |                            |
| RSDC-400 | 4.0 (101.6) | 3.0 (76.2)          |                            |
| RSDC-450 | 4.5 (114.3) | 3.5 (88.9)          | 11633-2                    |
| RSDC-500 | 5.0 (127.0) | 4.0 (101.6)         |                            |
| RSDC-550 | 5.5 (139.7) | 4.5 (114.3)         |                            |
| RSDC-600 | 6.0 (152.4) | 5.0 (127.0)         |                            |
| RSDC-650 | 6.5 (164.1) | 5.5 (139.7)         | 11633-3                    |
| RSDC-700 | 7.0 (177.8) | 6.0 (152.4)         |                            |
| RSDC-750 | 7.5 (190.5) | 6.5 (165.1)         |                            |
| RSDC-800 | 8.0 (203.2) | 7.0 (177.8)         | 11633-6                    |



RECOMMENDED MOUNTING HOLES  
PANEL THICKNESS: .047-.090 (1.2-2.3)

#### NOTES:

1. MATERIAL: NYLON 6/6 (RMS-48).
2. COLOR: NATURAL.

|             |                                       |                |
|-------------|---------------------------------------|----------------|
| F           | SEE ECN #831<br>FOR CHANGES           | SM<br>08.09.04 |
| E           | COMPLETELY REDRAWN                    | SM<br>02.11.02 |
| D           | REM. "NO TAMPER<br>AND RAMP" ON PRINT | JL<br>08.07.00 |
| C           | DIM. .225 (5.7)<br>WAS .255 (6.5)     | RS<br>01.25.93 |
| B           | DIM. "A" WAS REF.                     | RS<br>11.25.92 |
| A           | METRIC DIMS<br>CORRECTED              | RS<br>08.17.92 |
| R<br>E<br>V | DESCRIPTION                           | ENGR<br>DATE   |

TITLE: SNAP-IN CARD GUIDE



DWG IN  
IN (MM)



FINAL

|                                                                                |                                                     |                                                                                                  |                             |                     |
|--------------------------------------------------------------------------------|-----------------------------------------------------|--------------------------------------------------------------------------------------------------|-----------------------------|---------------------|
| TOLERANCES<br>UNLESS NOTED<br>.XX=±.010<br>.XXX=±.005<br>FRAC=±1/64<br>ANG=±1° | FILE # RSDC<br>MAT'L: SEE NOTES<br>RE: RICHCO, INC. | DWN: P.B.<br>DT: 04.-05-94<br>DT: RICHCO INC.<br>PO BOX 804238, CHICAGO, 60680<br>(773) 539-4060 | APP:<br>PART #<br>SEE TABLE | PRINT<br>TYPE<br>CA |
|--------------------------------------------------------------------------------|-----------------------------------------------------|--------------------------------------------------------------------------------------------------|-----------------------------|---------------------|