



CONTACT SIZE	SHELL SIZE	X	Y ±.040
16 SHORT	10SL, 14S, 16S	.087±.039	.079
16 LONG	14, 16, THRU 40	.260±.052	.102
12	14, 16, THRU 40	.118±.039	.102
4,8,0	14, 16, THRU 40	.091±.039	.102

REVISIONS			
ZONE	LTR	DESCRIPTION	DATE
	B	REDRAWN SEE RECORD DWG ECN:	9-23-92 SNYDER
	C	(CLII) SEE ECN 27941	1-28-93 SNYDER
	D	(CLII) WAS "O" NOTE 13,750 WELL DEPTH ECN:28347	12-21-93 SNYDER



10	1	10-581820-XX3	NUT	3,13
9	1	10-581819-XX1	SLEEVE	13
8	1	SEE COLUMN	GROMMET	12,13
7	SEE NOTE 10		CONTACT	
6	1	10-748XX-XXX	INSERT	
5	1	10-607XX-XX	GROMMET	
4	1	10-564869-XX	SLEEVE	
3	1	10-564868-XX3	NUT	3
2	1	10-101379-XX1	GASKET	9
1	1	SEE COLUMN	SHELL	

SEE SHEET 2

NOTES:

THE USE OF THIS DOCUMENT IS UNLIMITED. HOWEVER, DOCUMENTS REFERENCED HEREON MAY CONTAIN LIMITED RIGHTS DATA.

COMPANY ID: 2
CODED/MS/CUST: Y
INTERNAL: N
LOTNO: N
DATE CODE: 9-3895
SEE PRINT: N

UNLESS OTHERWISE SPECIFIED
LINEAR DIMENSIONS ARE IN INCHES.
TOLERANCES: .XXX±.010,
.XX ±.03, .X ±.1, ANGLES ±2°.
OTHER STANDARDS PER 9-3800
AND DOD-D-1000. NOTE REF=

FIND NO.	QTY REQD.	FSCM NO.	PART NUMBER	DESCRIPTION	NOTE REF.
PARTS LIST					
SPECIFICATIONS			AMPHENOL CORPORATION BENDIX CONNECTOR OPERATIONS SIDNEY, N.Y.		
MATERIAL SPEC. N/A			CONNECTOR, ELECTRICAL RECEPTACLE, REAR PANEL MOUNT, REVERSE BAYONET COUPLING, TYPE GTC030R V()-() SOLDERLESS		
PROCESS SPEC. SEE NOTE 5			U		
SIGNATURES			D. MACAVOY		
DATES			6-20-92		
APPROVED			71-581570-155		
1ST PART NO.			71-581560/579		
SCALE			NONE		
REF			N/A		
SHEET			1 OF 2		

COMPUTER GENERATED DRAWING

000000001

01653

TAB.

