


REV	ECN	APP'D
-	3600	JEC 12/11/98
A	4686	IQ 1/2/02
B	5137	

ELFK SERIES PART NUMBERING SCHEME



COLOR/PLATING
 0 : BLACK, TIN-LEAD (STANDARD)
 1 : BLACK, SELECTIVE GOLD
 G : GREEN, TIN-LEAD
 1G : GREEN, SEL. GOLD

MOUNTING EARS
 OE : BLACK, TIN-LEAD
 1E : BLACK, SEL. GOLD
 GE : GREEN, TIN-LEAD
 EG : GREEN, SEL. GOLD

CONSULT PCD FOR PART NO. AND AVAILABILITY OF FOLLOWING OPTIONS:

- * CUSTOM COLORS
- * CUSTOM MARKING
- * CUSTOM KEYING
- * SELECTIVE CONTACT LOADING



RATINGS

CURRENT - 15A
 VOLTAGE - 300V
 U.L. FILE NO. E83421



RATINGS

CURRENT - PENDING
 VOLTAGE - PENDING
 CSA FILE NO. LR69703


DIN VDE 0627:1986
 DIN VDE 0110-1:1989
 EN 60947-1:1991
 EN 60947-7-1:1992




CURRENT - PENDING
 VOLTAGE - PENDING
 TUV FILE NO. 20396

INSTALLATION RECOMMENDATIONS
 WIRE RANGE: AWG #14-26, STRANDED
 OR SOLID; AWG #12 STRANDED
 WIRE STRIP LENGTH: .310"
 TIGHTENING TORQUE: 7 LB-IN.



MATERIALS:
 HOUSING: PPO, UL 94 V-0
 CONTACT: COPPER ALLOY, NICKEL FINISH
 SCREW: STEEL, NICKEL FINISH
 WIRE CLAMP: COPPER ALLOY, NICKEL FINISH

MAX OPERATING TEMPERATURE:
 105°C

DIMENSIONS ANSI Y14.5M UNITS: INCHES Pro/E FILE	TOLERANCES .XX ±0.01 .XXX ±0.005 ANGLES ±2.0°	PROJECTION 	SPECIFICATION DRAWING ENGR D. MANTER 10-Dec-98				TITLE ELFK SERIES PLUG ASSEMBLY 45°			
ORIGINAL STAMPED IN RED	THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION WHICH IS THE CONFIDENTIAL PROPERTY OF PCD, INC. PEABODY, MA, USA		CHKD		SIZE A		DWG NO. ELFK02210		REV B	
			APPD J. CAHALY 12/11/98		CODE: 58982		SCALE: NONE	SHEET 1 OF 2		



L=NUM OF POS X CL SPACING



MOUNTING EARS CONFIGURATION

SIZE

A

DWG NO.

ELFK02210

REV

B

CODE: 58982

SCALE: NONE

SHEET 2 OF 2