



2P	Hook+Pillar
3P	Hook+Hook+Pillar
4P	Hook+Pillar+Hook+Pillar
5P	Hook+Pillar+Pillar+Hook+Pillar
5P over	Hook+Pillar+ ^{pillar} ...+Pillar+Hook+Pillar

DIM		TOL			
		2P-4P	5P-8P	9P-12P	13P-16P
Dim L	N×7.62-2.62	±0.15	±0.25	±0.30	±0.40
Dim P	(N-1)×7.62	±0.15	±0.25	±0.30	±0.40
Dim B	N×7.62+0.58	±0.15	±0.25	±0.30	±0.40

- Voltage rating: 300 V
- Current rating: 8 A
- Wire range:
- Solid wire(AWG): 12-28
- Stranded wire(AWG): 12-28
- Wire strip length: 8-9 mm
- Withstanding Voltage: 1.6KV
- Operating temperature: -40°C to +115°C
- Critical dimension: 

COLOR —
0: BLACK
5: GREEN
6: BLUE
8: GREY

— RoHS compliant
(lead<4%) 
In copper Alloy

— 0000: "@" Logo (Standard)
(Steel screw plating Cr)

000A: "ANYTEK" Mark
Any special item by
customer request.
please contact sales
department.

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE		HI 7.62mm With Flange Series					
PART NO.		HIxx30x2xxxxG		DWG NO.		8HI0204	
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.			Tolerance
		Dacheng 2012.08.22	Dacheng 2012.08.22		UNIT: mm		X. ±0.50
					SCALE: NONE		X.X ±0.30
					REV.: E		X.XX ±0.10
				SHEET: 01/01			X° ±1°