


LOC	DIST	P	F	ZONE	LTR	DESCRIPTION	DATE	APPD
DF	BO				G	REV & REDRAWN DF-4297	PY	11-91
					H	REV PER 0600-4161-95	JB	08-30-95



- 1 MATERIAL: PHENOLIC PER MIL-M-14, TYPE CFG OR MFH, COLOR: BLACK
- 2 MATERIAL: DIALLYL PHTHALATE PER MIL-M-14, TYPE SDG-F, COLOR: BLUE
- 3 AMP PART NO, DATE CODE, CSA CERT, AND ARROWS MARKED WITH WHITE INK OR BY LASER MARKING AT APPROX AREA SHOWN, EITHER SIDE
4. THIS MODULE WILL ACCOMMODATE:
- (2) TYPE XII FEMALE CONTACTS AND
 - (12) SUBMINIATURE COAXICON, TYPE II SIZE 16, TYPE III(+) SIZE 16 OR TYPE VI SIZE 16 SOCKET CONTACTS
5. THIS MODULE MATES WITH 202759

2	202760-4
1	202760-2
MATERIAL	PART NUMBER

DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN INCHES [mm] TOLERANCES ON : 2 PLC DEC ± - 3 PLC DEC ± .005 ANGLES ± - MATERIAL SEE TABLE FINISH - WEIGHT -				DR 9-12-91 P.YEAGER CHK 11-12-91 D.B.MUMMEY APPD 11-12-91 D.B.MUMMEY APPD - PRODUCT SPEC - APPLICATION SPEC - WEIGHT -		AMP AMP Incorporated Harrisburg, PA 17105-3608		PART NO	
						NAME		FEMALE BLOCK G SERIES, 14 POSN	
						SIZE	CAGE CODE	DRAWING NO	
						C	00779	202760	
						SCALE	4:1	SHEET	1 OF 1