



NOTES: UNLESS OTHERWISE SPECIFIED

1. FOR USE WITH RG-316 DOUBLE SHIELDED OR EQUIVALENT
2. MATERIAL SPECIFICATIONS:
INSULATORS: TEFLON, COLOR : NATURAL
SPACER: DELIN , COLOR: NATURAL
OUTER CONTACT: BERYLLIUM COPPER
ALL OTHER METAL PARTS: BRASS
3. FINISH SPECIFICATIONS:
CONTACT: .000003 MIN THICK GOLD OVER .000050 MIN THICK NICKEL
ALL OTHER METAL: THIN GOLD OVER .000050 MIN THICK COPPER
4. ELECTRICAL SPECIFICATIONS:
IMPEDANCE: 50 OHMS
FREQUENCY RANGE: DC TO 6 GHz
VSWR: 1.5 MAX
5. CAP, SPACER AND FERRULE SHIPPED LOOSE
6. CRIMP FERRULE (.151 HEX) AND SOLDER TO CONTACT PIN.



RECOMMENDED
CABLE STRIPPING DIMS



PER ASME Y14.5M-1994
UNLESS OTHERWISE SPECIFIED,
DIMENSIONS ARE IN INCHES [MM]
TOLERANCES:
DECIMAL: .XX [XX] ± .01 [0.3]
XXX [XXX] ± .005 [0.13]
XXXX [XXXX] ± .000X
ANGLES: ± 2° SCALE: XX

CUSTOMER
SALES DRAWING



WINCHESTER Winchester Electronics Corporation
ELECTRONICS 199 Park Road Ext Suite 104
Middlebury, Connecticut 06762

MCX RIGHT ANGLE FOR
RG-316 DOUBLE SHIELDED CABLE

DRAWN	DATE	APPROVED	DATE
MS	09/05/14	MAR	09/05/14
APPROVED	DATE	APPROVED	DATE
XXX	XX/XX/XX	XXX	XX/XX/XX

REV	DESCRIPTION	BY	DATE	APPD
A	ER054784	MS	09/05/14	MAR