





	Dim A	Dim B
2-6p	± 0.15	± 0.15
7-12p	± 0.25	± 0.25
13-18p	± 0.30	± 0.30
19-24p	± 0.40	± 0.40

TS xx 71 X D XXXX G

RoHS
Pb<40,000ppm

Color
0000: "@" Logo

0 Black (RAL9005)
2 Red (RAL3001/D)
3 Orange(RAL2011/P)
4 Yellow(RAL1018/A)
5 Green(RAL6018/T)
6 Blue (RAL5015/A)
8 Grey(RAL7035/D)

000A: "ANYTEK" Mark
0091: "ANYTEK" Mark
Any special item by
customer request.
please contact sales
department.

```
02 2 CONTACTS
03 3 CONTACTS
... ..
24 24 CONTACTS
```

Color

Black (RAL9005)

Red (RAL3001/D)

Orange(RAL2011/P)

Yellow(RAL1018/A)

Green(RAL6018/T)

Blue (RAL5015/A)

Grey(RAL7035/D)

0000: "@" Logo
000A: "ANYTEK" Mark
0091: "ANYTEK" Mark
Any special item by
customer request.
please contact sales
department.

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	TS-5.0mm Series(W/latching hooks on the back side) With flange						
PART NO.	TSxx71xDxxxxG			DWG NO.	8TS0004 		
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.			Tolerance
			Chen Bo 2010.08.16		UNIT: mm	X. ±0.50	
					SCALE: NONE	X.X ±0.30	
				SHEET: 01/01	REV: I	X.XX ±0.10	
						X° ±1°	