

330-003 and 330-004 Pipe Thread Adapter Direct Coupling



33

CONNECTOR DESIGNATORS A-B*-C-D-E-F G-H-J-K-L-S

* Conn. Design. B See Note 3

DIRECT COUPLING





TABLE II: STANDARD FINISHES

GLENAIR	
SYMBOL	FINISH
B	Cadmium Plate, Olive Drab
C	Anodize, Black
G	Hard Coat, Anodic
M	Electroless Nickel
NF	Cadmium Plate, Olive Drab Over Electroless Nickel

See Back Cover for Complete Finish Information and Additional Finish Options

See inside back cover fold-out or pages 13 and 14 for unabridged Tables I and II.

TABLE III: CABLE ENTRY

Dash No.	Pipe Thread	E	F Dia	G Dia	Length	
					Min	Desig.
01	1/8	.391 (9.9)	.405 (10.3)	.500 (12.7)	2.0 (50.8)	4
02	1/4	.593 (15.1)	.540 (13.7)	.625 (15.9)	2.0 (50.8)	4
03	3/8	.593 (15.1)	.675 (17.1)	.875 (22.2)	2.0 (50.8)	4
04	1/2	.781 (19.8)	.840 (21.3)	1.000 (25.4)	2.5 (63.5)	5
05	3/4	.812 (20.6)	1.050 (26.7)	1.250 (31.8)	2.5 (63.5)	5
06	1	1.000 (25.4)	1.315 (33.4)	1.500 (38.1)	2.5 (63.5)	5
07	1 1/4	1.031 (26.2)	1.660 (42.2)	1.750 (44.5)	3.0 (76.2)	6
08	1 1/2	1.031 (26.2)	1.900 (48.3)	2.125 (54.0)	3.0 (76.2)	6
09	2	1.062 (27.0)	2.375 (60.3)	2.500 (63.5)	3.0 (76.2)	6
10	2 1/2	1.453 (36.9)	2.875 (73.0)	3.250 (82.6)	3.0 (76.2)	6

1. Pipe threads per American standard taper pipe thread.
2. Metric dimensions (mm) are indicated in parentheses.
3. When using Connector Designator B refer to pages 18 and 19 for part number development.