




7. CABLE ACCOMMODATION DIMS:
JACKET DIA.----- .088 MAX.
DIELECTRIC DIA.----- .032-.042
INNER CONDUCTOR DIA.--- .009-.019
FOR USE WITH EXTRUDED OR WRAPPED JACKET.

6. FOR ELECTRICAL & MECHANICAL
SPECS. SEE MALCO CATALOG.

5. .016 DIA. WIRE HOLE 3 PLACES

4. DELETED

3. GOLD PLATE PER MIL-G-45204 TYPE II, GR.C, CL.I
2. SEE RF-ASMB-8 ASSY INSTRUCTIONS. SPECIAL TOOL REQ'D:
CONTACT CRIMP: 010-0134-0000 & LOCATOR 001-0104-0000.
ALTERNATE TOOL 010-0065-0000 (NO LOCATOR REQUIRED)
HOUSING CRIMP: 010-0081-0000.

1. THIS CONNECTOR MATES WITH ALL 50Ω
GOLDEN CRIMP, CRIMP SILVER & ALL S-50 JACKS &
RECEPTACLES AS LISTED IN MICRODOT CATALOG.

NOTES: UNLESS OTHERWISE SPECIFIED

TYCO CUSTOMER
DWG 7-1532149-6

					DELETED		11
1	1	1	1	003-0815-0001	SEALING SLEEVE	SILICONE RUBBER MIL-R-5847	10
3	1	1	1	003-0813-0002	MIDDLE SLEEVE	LEADED COPPER	9
3	1	1	1	003-0814-0002	INNER SLEEVE	BRASS, QQ-B-626	8
1	1	1	1	003-0811-0001	CABLE INSULATOR	TEFLON PER L-P-403	7
1	1	1	1	003-1301-0001	BODY INSULATOR	TEFLON PER L-P-403	6
3	1	1	1	003-0807-0002	PIN CONTACT	COPPER ALLOY	5
3	1			003-1299-0004	HOUSING SUB-ASSY NUT-1/4" HEX W/WIRE HOLES		4
3		1		003-1299-0003	HOUSING SUB-ASSY NUT-1/4" HEX		3
3			1	003-1299-0002	HOUSING SUB-ASSY NUT-1/4" KNURL		2
3			1	003-1299-0001	HOUSING SUB-ASSY NUT-1/4" PARTIAL HEX		1
4	3	2	1	COMPONENT	NOMENCLATURE	MAT'L & SPEC.	ITEM

ASSEMBLY		NO. REV.		DATE		BY		APP.		STANDARD TOLERANCES UNLESS OTHERWISE SPECIFIED		MALCO A MICRODOT COMPANY, INC. 220 PASADENA AVE., SO. PASADENA, CALIF.	
NEXT ASS'Y REQ'D		LET		SCD		REV. LETTER		DATE		APP.		SURFACE TREATMENT NOTED	
												MATERIAL NOTED	
												APP. R.B.C.	
												APP. J.L. 7/1/65	
												CHECKED BY	
												DRAWN BY U.M.	
												SCALE	
												DATE	
												DRAWING NUMBER	
												CDM 132-0112-000* J	

PLUG ASSEMBLY
NON-ENVIRONMENTAL
GOLDEN CRIMP 50Ω

PROD. CODE
941
CODE
CDM 132-0112-000* J