






LOC	DIST	REVISIONS					
AD	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			H	REVISED PER ECO-11-006183	27SEP11	KH	JO



		71.83 [2.828]	63.91 [2.516]	62.23 [2.450]	49	100	6-104893-0
三		65.48 [2.578]	57.56 [2.266]	55.58 [2.200]	44	90	5-104893-9
		59.13 [2.328]	51.21 [2.016]	49.53 [1.950]	39	80	5-104893-8
		52.78 [2.078]	44.86 [1.766]	43.18 [1.700]	34	70	5-104893-7
	△△	46.43 [1.828]	38.51 [1.516]	36.83 [1.450]	29	60	5-104893-6
		40.08 [1.578]	32.16 [1.266]	30.48 [1.200]	24	50	5-104893-5
		33.73 [1.328]	25.81 [1.016]	24.13 [.950]	19	40	5-104893-4
		27.38 [1.078]	19.46 [.766]	17.78 [.700]	14	30	5-104893-3
		21.03 [.828]	13.11 [.516]	11.43 [.450]	9	20	5-104893-2
		14.68 [.578]	6.76 [.266]	5.08 [.200]	4	10	5-104893-1
	△5	76.96 [3.030]	43.59 [1.716]	41.91 [1.650]	33	68	1-104893-1
		71.83 [2.828]	63.91 [2.516]	62.23 [2.450]	49	100	1-104893-0
三		65.48 [2.578]	57.56 [2.266]	55.58 [2.200]	44	90	104893-9
		59.13 [2.328]	51.21 [2.016]	49.53 [1.950]	39	80	104893-8
		52.78 [2.078]	44.86 [1.766]	43.18 [1.700]	34	70	104893-7
	△2	46.43 [1.828]	38.51 [1.516]	36.83 [1.450]	29	60	104893-6
		40.08 [1.578]	32.16 [1.266]	30.48 [1.200]	24	50	104893-5
		33.73 [1.328]	25.81 [1.016]	24.13 [.950]	19	40	104893-4
		27.38 [1.078]	19.46 [.766]	17.78 [.700]	14	30	104893-3
		21.03 [.828]	13.11 [.516]	11.43 [.450]	9	20	104893-2
		14.68 [.578]	6.76 [.266]	5.08 [.200]	4	10	104893-1
FINISH	D	C	B	A	NO OF POSN	PART NO	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DIN 17-6-93 J. HERRINGTON CHK P. SREMCIICH 24-6-93		 TE Connectivity	
DIMENSIONS: mm [INCHES]		TOLERANCES, UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ± 2 PLC ± 0.36 [015] 3 PLC ± 4 PLC ± ANGLES ± ±		NAME APVD D. DUPLER 24-6-93 PRODUCT SPEC 108-1443 APPLICATION SPEC 114-7010	
MATERIAL  SEE TABLE		WEIGHT —		SIZE CAGE CODE DRAWING NO A1 00779 C-104893	
		CUSTOMER DRAWING		SCALE 10:1 SHEET 1 OF 1 REV H	