


- I : AS SHOWN



```

1.MATERIAL  : CASE HOUSING-POLYCARBONATE.
              TERMINAL HOUSING-NYLON.
              CONTACT-COPPER ALLOY.
              SHELL-COPPER ALLOY.
2.FINISH   : CONTACT-UNDERPLATE: Ni
              CONTACT AREA: Au
              SHELL: Ni

```

CONTACT NO.	WIRE COLOR	
	568A	568B
1	WHITE / GREEN	WHITE / ORANGE
2	GREEN	ORANGE
3	WHITE / ORANGE	WHITE / GREEN
4	BLUE	BLUE
5	WHITE / BLUE	WHITE / BLUE
6	ORANGE	GREEN
7	WHITE / BROWN	WHITE / BROWN
8	BROWN	BROWN

DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:	
單位:	耗	一般公差	
mm		0 PLC	± 0.3
		1 PLC	$\pm$
		2 PLC	$\pm$
		3 PLC	$\pm$
		4 PLC	$\pm$
		ANGLES	± 3

MATERIAL		FINISH	
材料	-	仕上	-

DWN	29NOV2005
J. AKASAKA	
CHK	1DEC2005
D. MITSUGI	
APVD	1DEC2005
D. MITSUGI	
PRODUCT SPEC	
製品規格	
108-78381	
APPLICATION SPEC	
取付適用規格	
114-5402	

CUSTOMER DRAWING

WIRE RANGE 综合电線断面積		INSULATION DIA 被覆外径	
-		Ø 6.5	
		TE Connectivity	
NAME 名称			
RJ 45 CONNECTOR INDUSTRIAL ETHERNET IP20 8POS 180DEG STRD WIRE			
SIZE	CAGE CODE	DRAWING NO 番号	RESTRICTED TO
A3	-	C-1903527	-
SCALE 尺度		SHEET	OF
1		1	REV B1