


| SIGN                                           | DATE     | DESCRIPTION     | APPROVER |
|------------------------------------------------|----------|-----------------|----------|
| △                                              | 04/07'10 | Add the 2P mark | RUNNER   |
| THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!! |          |                 |          |



### Material

- Item a Terminal body:Thermoplastic ( UL94V-0 )
- Item b Terminal body:Thermoplastic ( UL94V-0 )
- Item c Terminal lever:Thermoplastic ( UL94V-0 )
- Item d Wire guard:Stainless Steel
- Item e Female contact:PhBz ( CuSn ) Tin plated

### Electrical cULus

- Voltage rating:300V
- Current rating:10A
- Solid wire(AWG):12-26
- Stranded wire(AWG):12-26
- Wire strip length:9-10mm
- Withstanding Voltage:1.6KV
- Operating temperature:-40°C to +115°C
- Safety Approval:  us

H4 xx 70 x B xxxx G

|     |             |   |       |                                                                        |                   |              |
|-----|-------------|---|-------|------------------------------------------------------------------------|-------------------|--------------|
| 02  | 2 CONTACTS  | 0 | Black | 0000                                                                   | Standard @ Logo   | RoHS         |
| 03  | 3 CONTACTS  | 5 | Green | 000A                                                                   | Standard ANY Logo | Pb<40,000ppm |
| ... | ...         | 6 | Blue  | Any special item by customer request, please contact sales department. |                   |              |
| 24  | 24 CONTACTS | 8 | Grey  |                                                                        |                   |              |

# ANYTEK

## CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD


|          |               |                                                     |                    |              |                                                                                                                                                                                          |            |
|----------|---------------|-----------------------------------------------------|--------------------|--------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|------------|
| TITLE    |               | H4 5.0 Series (hook on back side ( Without flange ) |                    |              |                                                                                                                                                                                          |            |
| PART NO. | H4xx70xBxxxxG |                                                     |                    | DWG NO.      | 8H40102                                                                                                                                                                                  |            |
| APPROVED | CHECKED       | DESIGNED                                            | DRAWN              | CUST NO.     | <div>   </div> |            |
|          |               | Runner<br>2010.04.07                                | Tony<br>2009.03.12 |              |                                                                                                                                                                                          |            |
|          |               |                                                     |                    | SHEET: 01/01 | UNIT: mm                                                                                                                                                                                 | X. ±0.50   |
|          |               |                                                     |                    |              | SCALE: NONE                                                                                                                                                                              | X.X ±0.30  |
|          |               |                                                     |                    |              | REV.: C                                                                                                                                                                                  | X.XX ±0.10 |
|          |               |                                                     |                    |              |                                                                                                                                                                                          | X* ±1*     |

### Dimension


|       |            |
|-------|------------|
| DIM A | N×5.0+0.10 |
| DIM B | ( N-1)×5.0 |

N=Number of poles

| POLES   | TOL   |
|---------|-------|
| 2p-6p   | ±0.15 |
| 7p-12p  | ±0.25 |
| 13p-16p | ±0.35 |
| 17p-24p | ±0.40 |



SECTION A-A



2P

