

MICRO SWITCH



A DIVISION OF MINNEAPOLIS HONEYWELL REGULATOR COMPANY
FREEPORT, ILLINOIS

FED. MFR. CODE 91929



ASSEMBLY-
TOGGLE SWITCH

CATALOG LISTING

22AT21-T



N.C. TO C. CIRCUIT MADE (ALL SWITCHES) (MAINTAINED POSITION).
N.O. TO C. CIRCUIT MADE (SWITCHES 5, 6, 7, AND 8)
N.C. TO C. CIRCUIT MADE (SWITCHES 1, 2, 3, AND 4) (MOMENTARY POSITION).



NOTE-

- 1-UNIT INCLUDES (8) CAT. LIST. ISM3-T BASIC SWITCH.
2-SWITCHES DO NOT NECESSARILY OPERATE SIMULTANEOUSLY.
3-TERMINALS ARE PLATED FOR SOLDERING.
4-UNIT WILL PERFORM SATISFACTORILY IN TEMPERATURES FROM 250°F TO MINUS 65°F.

CHARACTERISTICS

ELECTRICAL DATA

CONTACT ARRANGEMENT
(8) S.P.D.T.

250 VAC	5 AMP
30 VOLTS DC RATING	
INDUCTIVE	SEA LEVEL 3 AMP
	50,000 FT. 2.5 AMP
RESISTIVE	SEA LEVEL 5 AMP
	50,000 FT. 5 AMP
MAXIMUM INRUSH	24 AMP

SCALE- FULL

DO NOT SCALE PRINT

UNLESS OTHERWISE
SPECIFIED
DIMENSIONS ARE IN INCHES

TOLERANCES ARE:

ONE PLACE	(.0)	±.030
TWO PLACE	(.00)	±.015
THREE PLACE	(.000)	±.005
ANGLES		± 1°

WEIGHT

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

22AT21-T

M

DRAWING
NUMBER

287

X 2

IS

287

REPLACES

RELEASE NO. SR8725

CHECK

REVISIONS

A CORR.

N.H.L.

30 NOV. 56

B CORR.

K.A.F.

8 DEC. 56

C WAS

SK14162

L.M.H.

18 MAR 59

D SR8725

L.S.D.

6 JAN 60

E CO18298

D WV

1 AUG 63

F CO

50566-B

WJM

6 MAY 82

CHECK

644

644

644

644

644

644

644

644

644

644

644

644

644

74-96.3

DRAWN

56

OCT.

24

K.A.F.