







SECTION A-A



N = Number of poles  
 Dim L = N x 5.0  
 Dim P = (N - 1) x 5.0

| Dim.<br>Poles | Dim L | Dim P |
|---------------|-------|-------|
| 2-6p          | ±0.15 | ±0.15 |
| 7-12p         | ±0.25 | ±0.25 |
| 13-18p        | ±0.35 | ±0.35 |
| 19-24p        | ±0.40 | ±0.40 |

| SIGN                                           | DATE     | DESCRIPTION        | APPROVER |
|------------------------------------------------|----------|--------------------|----------|
| △                                              | 07/09'13 | update the drawing | Guoxue   |
| THIS IS CAD DRAWING, DO NOT REVISE MANUAL Y!!! |          |                    |          |

#### Materials

- Item a Terminal housing : PA66 ( UL94V-0 )
- Item b Terminal screw: Steel Zinc plating "+/-" slot type
- Item c Wire guard : Stainless steel
- Item d Terminal body: Brass(CuZn) ,Tin Plated

#### Electrical cULus

- Voltage rating: 300VAC
- Current rating: 15A
- Wire range:
- Solid wire(AWG): 12-26
- Stranded wire(AWG): 12-26
- Torque(Lb-In): 3.5
- Screw: M2.6
- Wire strip length: 5-6mm
- Withstanding Voltage: 1.6KV
- Operating temperature: -40°C to +115°C
- △ ● Soldering temperature: 260°C±5°C/5 Sec
- △ ● Safety Approval: cULus
- Critical dimension: ∇

△ KZ xx 7 0 x 1 xxxx G

End stackable  
 02 2 POLES  
 03 3 POLES  
 ...  
 24 24 POLES

COLOR

- 0 Black
- 2 Red (RAL3001/D)
- 3 Orange(RAL2011/P)
- 4 Yellow(RAL1018/A)
- 5 Green(RAL6018/T)
- 6 Blue (RAL5015/A)
- 8 Grey(RAL7035/D)
- 9 White
- C Green(RAL 6018/U)

RoHS compliant  
 (lead<4%)  
 In copper Alloy

0000: "@" Logo (Standard)  
 000A: "ANYTEK" Mark

Any special item by  
 customer request.  
 please contact sales  
 department.

# ANYTEK

## CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

|              |               |                                       |                      |                                                                                       |             |           |
|--------------|---------------|---------------------------------------|----------------------|---------------------------------------------------------------------------------------|-------------|-----------|
| TITLE        |               | KZ 5.0 Series ("+"-"Screw&Round hole) |                      |                                                                                       |             |           |
| PART NO.     | KZxx70x1xxxxG |                                       |                      | DWG NO.                                                                               | 8KZ0102     |           |
| APPROVED     | CHECKED       | DESIGNED                              | DRAWN                | CUST NO.                                                                              | Tolerance   |           |
|              |               | Guoxue<br>2013.07.09                  | Guoxue<br>2013.07.09 |  | UNIT: mm    | X. ±0.5   |
|              |               |                                       |                      |                                                                                       | SCALE: NONE | X.X ±0.3  |
|              |               |                                       |                      |                                                                                       | REV: C      | X.XX ±0.1 |
| SHEET: 01/01 |               |                                       |                      |                                                                                       | X° ±1°      |           |