





REV.	ECN NO.	DATE	SIGN	DESCRIPTION
D	C210309	2021/03/04	Ruru	 X4
E	C230012	2023/01/05	Vicky	 X1
F	C231037	2023/08/08	Vicky	 X1




MSAP-XXPFFP-SF8002
XX: No. Of Pin 

Recommended
Panel Cut-Out



△ Note:


- * RoHS Compliant
- *  Important dimension
- *  Waterproof rate: IP68, unmated 1m/24h
- *  IP69K, mated
- * Connector
 - Housing: Thermoplastic, Black
 - Pin: Copper alloy, Gold plated
 - O-Ring: Rubber, Gray
- * Shield: Thermoplastic, Black
- * Nut: Thermoplastic, Black
- * O-Ring: Rubber, Gray
- * For panel thickness max: 4.0mm
- * Nut is packed separately in pe bag



Pin Assignment Front View

UNIT:mm				TITLE N SEN, M12 A -PLASTIC, SCREW RECEPTACLE, F, F, PCB S			Amphenol LTW 安費諾亮泰企業股份有限公司		ITEM NO		DRAWN BY Lingpeng		DATE 2017-09-19				
TOLERANCE .X ±0.25 .XX ±0.1 .XXX ±0.05 ANGLES ±				SCALE 3:2		SIZE A4			SHEET 1 OF 2		DWG NO MSAP-XXPFFP-SF8002		CHECKED BY Mafei		DATE 2017-09-19		
				REV. F		WC-REV. .0			QC: Inspection item		CUSTOMER ALTW		APPROVED BY Jerry		DATE 2017-09-19		

F
E
D
C
B
A



8P

W

安費諾亮泰企業股份有限公司

DATE

2017-09-19

	DATE
--	------

2017-09-19

	DATE
--	------

2017-09-19

TOLERANCE	
.X	±0.25
.XX	±0.1
.XXX	±0.05
ANGLES	±1°

SHEET	2	OF	2
-------	---	----	---

QC: Inspection item