

6

5

4

3

2

1

D

D

C






C

B

B

A

A

**NOTES:****1. MATERIALS AND FINISHES:**

BACKSHELL AND BACKSHELL COVER: PRECISION-MACHINED ALUMINUM, ELECTROLESS NICKEL PLATE.



BACKSHELL COVER GASKET: SILICONE NICKEL GRAPHITE.

JACKSCREWS, WASHERS AND WAVE WASHERS: STAINLESS STEEL, PASSIVATED.

EMI CLIP: BERYLLIUM COPPER.

KNOBS, SET SCREWS, BACKSHELL COVER SCREWS, GROUNDING SCREWS: STAINLESS STEEL, PASSIVATED.

**2. DETAILED PRODUCT, ELECTRICAL AND MECHANICAL INFORMATION IS AVAILABLE IN THE LATEST STANDARD DENSITY MACH-D PRODUCT PUBLICATION AT CONNECTPOSITRONIC.COM.****3. COMPONENTS ARE COMPLIANT TO CURRENT RoHS DIRECTIVES.**

BY ND		CHK AB	3RD ANGLE 		<div>POSITRONIC BELIEVES THE DATA ON THE DRAWING TO BE RELIABLE. THE USER EMPLOYS SUCH INFORMATION AT HIS OWN DISCRETION AND RISK. POSITRONIC ASSUMES NO RESPONSIBILITY FOR RESULTS OBTAINED OR DAMAGES INCURRED FROM USE OF SUCH INFORMATION IN WHOLE OR IN PART.</div> <div><div>Positronic® CONNECTPOSITRONIC.COM</div></div>	
APR PA		RELEASED DATE: 2022-03-15		SCALE NTS		
TOLERANCES ±0.03mm [.001 INCHES]FOR MALE CONTACT MATING DIAMETERS ±0.08mm [.003 INCHES]FOR CONTACT TERMINATION DIAMETERS ±0.13mm [.005 INCHES]FOR ALL OTHER DIAMETERS ±0.38mm [.015 INCHES]FOR ALL OTHER DIMENSIONS ±5° FOR ALL ANGLES DIMENSION ARE IN MILLIMETERS [INCHES]						
PART NUMBER MCD15000ENE50/AA			TITLE MCD15000ENE50/AA		SERIES MCD	
CREATED ON: 2022-03-03			SHEET SHEET 1 OF 1		REV A	

6

5

4

3

2

1