



THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.



LOC	DIST	REVISIONS				
AD	00	P	LTR	DESCRIPTION	DATE	APVD
			G2	REVISED PER ECO-12-013195	18JUL12	KH

D




DETAIL FOR -1 ONLY
(2 POSITION)

C



B



A

2.498	2.400	24	25	2-104503-4
2.398	2.300	23	24	2-104503-3
1.998	1.900	19	20	1-104503-9
1.598	1.500	15	16	1-104503-5
1.498	1.400	14	15	1-104503-4
1.398	1.300	13	14	1-104503-3
1.298	1.200	12	13	1-104503-2
1.198	1.100	11	12	1-104503-1
1.098	1.000	10	11	1-104503-0
.998	.900	9	10	104503-9
.898	.800	8	9	104503-8
.798	.700	7	8	104503-7
.698	.600	6	7	104503-6
.598	.500	5	6	104503-5
.498	.400	4	5	104503-4
.398	.300	3	4	104503-3
.298	.200	2	3	104503-2
.198	.100	1	2	104503-1
C	B	A	NO OF POSN	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN D KEITZER 12-21-88		 TE Connectivity				
DIMENSIONS: INCHES		CHK H. MOLL 12-22-88						
	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± .005 4 PLC ± - ANGLES ± -		APVD C. SINISI 12-22-88	NAME PIN HOUSING, AMPMODU® MTE, SINGLE ROW, .100 C/L, WITH GUIDE RIBS				
			PRODUCT SPEC 108-25034					
			APPLICATION SPEC 114-25026	SIZE A2	CAGE CODE 00779	DRAWING NO C=104503	RESTRICTED TO -	
			MATERIAL FLAME RETARDANT THERMOPLASTIC, COLOR: BLACK	FINISH -	WEIGHT -			
			CUSTOMER DRAWING			SCALE 4:1	SHEET 1 of 1	REV G2