




1. THIS CONNECTOR ACCEPTS SEVEN (7) SIZE 16 MULTIMATE SOCKET CONTACTS. MAXIMUM WIRE INSULATION DIA = 2.67 [.105].

2. RECEPTACLE MATES WITH AMP PART NUMBER 208716-1.

3. AMP PART NUMBER & DATE CODE TO BE LOCATED ON EDGE OF FLANGE.

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.

DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm [INCHES] TOLERANCES ON:

2 PLC DEC ± 0.13 [.005]

3 PLC DEC ± -

ANGLES ± -

MATERIAL SEE CALLOUTS

FINISH SEE CALLOUTS

DR 09-07-94 D.HARDY

CHK 09-09-94 R.STONE

APPD 09-30-94 A.FRANTUM

APPD 09-30-94 A.FRANTUM

PRODUCT SPEC -

APPLICATION SPEC -

WEIGHT -

208717-1

PART NO

AMP AMP Incorporated Harrisburg, PA 17105-3608

NAME RECEPTACLE ASSEMBLY, 14-7, REVERSE SEX, CMC

SIZE B

CAGE CODE 00779

DRAWING NO C-208717

SCALE 2:1

SHEET 1 OF 1

AMP 1470-15 REV 3-92

07-SEP-94 13:19:11 amp35397 /home/sa026a/dept4023/amp35397/edmod

CUSTOMER DRAWING