

4

3



2

1

© - TE Connectivity. All Rights Reserved.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
M		REVISED PER ECO-20-000170	21MAY2020	KR	JO



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	15AUL75	TE Connectivity Ltd.	
		CHK	15AUL75		
		APVD	16AUL75	NAME	
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC	
INCHES				APPLICATION SPEC	
				WEIGHT	
				CUSTOMER DRAWING	
				SCALE 5:1	
				SHEET 1 of 2	
				REV M	

REVISIONS					
P	LYR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-

- 1

.000015 MIN. GOLD OVER .000050 MIN. NICKEL IN CONTACT AREA
- 2

.000030 MIN. GOLD OVER .000050 MIN. NICKEL IN CONTACT AREA
- 3

ALL PARTS ASSEMBLED IN MEXICO MUST BE STAMPED "ASSY IN MEXICO"
THE WORD "MEXICO" CAN BE SUBSTITUTED ONLY WHERE PART SIZE
PROHIBITS STAMPING "ASSY IN MEXICO" INK STAMP COLOR WHITE OR HOT
STAMP (NO WHITE TAPE) 115-9009, APPROX. WHERE SHOWN, SIDE OPTIONAL.
- 4

MATTE TIN PLATED CONTACT TAILS

4	.437	8-530677-3	7.557	7.012	7.307	6.872	6.552	43	
4	.370	7-530677-4	3.189	2.644	2.939	2.504	2.184	15	
4	.370	7-530677-1	1.785	1.240	1.535	1.100	.780	6	
	.437	3-530677-3	7.557	7.012	7.307	6.872	6.552	43	1-530677-3
	.370	3-530677-2	5.217	4.672	4.967	4.532	4.212	28	1-530677-2
	.437	3-530677-1	7.713	7.168	7.463	7.028	6.708	44	1-530677-1
	.437	3-530677-0	6.465	5.920	6.215	5.780	5.460	36	1-530677-0
	.437	2-530677-9	5.529	4.984	5.279	4.844	4.524	30	530677-9
	.370	2-530677-8	4.749	4.204	4.499	4.064	3.744	25	530677-8
	.370	2-530677-7	4.593	4.048	4.343	3.908	3.588	24	530677-7
	.370	2-530677-6	4.281	3.736	4.031	3.596	3.276	22	530677-6
	.370	2-530677-5	3.657	3.112	3.407	2.972	2.652	18	530677-5
	.370	2-530677-4	3.189	2.644	2.939	2.504	2.184	15	530677-4
	.370	2-530677-3	3.721	2.176	2.471	2.036	1.716	12	530677-3
	.370	2-530677-2	2.409	1.864	2.159	1.724	1.404	10	530677-2
	.370	2-530677-1	1.785	1.240	1.535	1.100	.780	6	530677-1
	W	PART NO. 2	F	D	C	B	A	NO OF POSN.	1 PART NO.

OBSOLETE

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 15AUL75	 TE Connectivity Ltd.		
DIMENSIONS: INCHES		OK 15AUL75			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD 16AUL75	NAME		
0 PLC ± .005 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± - FINISH		PRODUCT SPEC		HOUSING ASSY, LOW PROFILE EDGE CONNECTOR. FLOW SOLDER POST FOR .052 DIA. HOLE, .156 X .200 CENTERS	
MATERIAL		APPLICATION SPEC			
		SIZE	GAGE CODE	DRAWING NO	RESTRICTED TO
		A2	00779	C=530677	-
		CUSTOMER DRAWING			SCALE 5:1 SHEET 2 of 2 REV M