

MICRO SWITCHA DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR COMPANY
PASADENA, CALIFORNIA

FED. MFR. CODE 91929

ACTUATOR - SWITCH

CATALOG LISTING

JX - 44**JX - 44**

REPLACES

RELEASE NO. SR-10742

MDRAWING
NUMBER**28****33**

ISSUE

33

REVISIONS

A CO15829

M B F

17 APRIL 61

B SR-10742

R E R

18 JAN 63

C CO22579

O M W

1 MAY 67

D CO23793

W E B

6 FEB 68

E CO22579

M B S

19 APR 68

F CO30270

S R H

29 FEB 72

G CO62929

D L T

13 MAY 96

CHECK

29 AUG 60

FWF

CHECK

6 FEB 68

CHECK

21 JAN 63

GCH

CHECK

60

DRAWN

K L B

29 AUG 60

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR CO. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CHARACTERISTICS WITH ISKI-T BASIC
SWITCH INSTALLED

OPERATING FORCE — — — — 7 OZ MAX

RELEASE FORCE — — — — 2 OZ MIN

DIFFERENTIAL TRAVEL — — — .025 MAX

OVERTRAVEL — — — — .015 MIN

ELECTRICAL DATA

CONTACT ARRANGEMENT

BREAK DISTANCE

SCALE 2 TO 1



DO NOT SCALE PRINT

UNLESS OTHERWISE
SPECIFIED

DIMENSIONS ARE IN INCHES

TOLERANCES ARE:ONE PLACE (.0) ±.030
TWO PLACE (.00) ±.015
THREE PLACE (.000) ±.005
ANGLES ±

WEIGHT



NOTE -

① SLIGHT ROTATION BETWEEN BASIC AND ACTUATOR MAY BE NECESSARY
TO OBTAIN OPERATING POSITION, BASED ON USING
NO. 2-56 MACHINE SCREWS