









	1	2	3	4	5	6	7	8			
F					REV.	ECN NO.	DATE	SIGN	DESCRIPTION		
					C		2020/04/17	JC Chen	 X2		
					D	C210561	2021/04/14	Vicky	 X3		
E	C230009	2023/01/03	Vicky	 X1							
E											
D											
C											
B					 Note: * RoHS Compliant *  Important Dimension  * Waterproof rate: IP67, mated Connector Housing: Thermoplastic, Black Pin: Copper alloy, Gold plated Extension Nut: Thermoplastic, Black Nut: Thermoplastic, Black O-Ring: Rubber, Gray * Clamp Ring: Thermoplastic, Black * Sealing Nut: Thermoplastic, Black  * Seal: Rubber, Gray, OD:Ø4.0mm~Ø7.0mm * One set unassembled in one pe bag						
A	UNIT:mm   TITLE N SEN, M12 A -PLASTIC, SCREW CABLE W/O SR, F, F, FI SOLDER SCALE 1:1 SIZE A4 SHEET 1 OF 1 REV. E WC-REV. .0  QC:Inspection item				ITEM NO DWG NO MSAP-XXBFFA-SR7001 CUSTOMER ALTW DRAWN BY Yulong_wang CHECKED BY Jinhai APPROVED BY Jerry DATE 2016-07-22 DATE 2016-07-22 DATE 2016-07-22						
				Amphenol LTW				安費諾亮泰企業股份有限公司			
								W10814-03-0001A2			