


THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION



© COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
CM	00		A	WR-08-38	13AUG2008	KW	CC


POSITION 1
IDENTIFICATION
FEATURE




MATERIAL: HOUSING: NYLON, UL94V-0, BLACK
CONTACTS: BRASS, TIN-PLATED



24	46.2±0.25 [1.82±.01]	51.6 [2.03]	55.6 [2.19]	2-2029134-4
22	42.0±0.25 [1.65±.01]	47.4 [1.87]	51.4 [2.02]	2-2029134-2
20	37.8±0.25 [1.49±.01]	43.2 [1.70]	47.2 [1.86]	2-2029134-0
18	33.6±0.25 [1.32±.01]	39.0 [1.54]	43.0 [1.69]	1-2029134-8
16	29.4±0.25 [1.16±.01]	34.8 [1.37]	38.8 [1.53]	1-2029134-6
14	25.2±0.25 [.99±.01]	30.6 [1.21]	34.6 [1.36]	1-2029134-4
12	21.0±0.25 [.83±.01]	26.4 [1.04]	30.4 [1.20]	1-2029134-2
10	16.8±0.13 [.66±.005]	22.2 [.87]	26.2 [1.03]	1-2029134-0
8	12.6±0.13 [.50±.005]	18.0 [.71]	22.0 [.87]	2029134-8
6	8.4±0.13 [.33±.005]	13.8 [.54]	17.8 [.70]	2029134-6
4	4.2±0.13 [.17±.005]	9.6 [.38]	13.6 [.54]	2029134-4
2	-	5.4 [.21]	9.4 [.37]	2029134-2
POS	A	B±0.25[.01]	C±0.38[.015]	PART NUMBER



PCB LAYOUT: COMPONENT SIDE
RECOMMENDED BOARD THICKNESS 1.78 [.070]



THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm [INCHES]

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	±
1 PLC	± 0.13 [.005]
2 PLC	± 0.25 [.010]
3 PLC	± -
4 PLC	± -
ANGLES	±
FINISH	±

MATERIAL

DWN
K. WHITAKER
CHK
C. CASH
APVD
C. CASH
PRODUCT SPEC

13AUG2008
13AUG2008
13AUG2008

Tyco Electronics

Tyco Electronics Corporation
Harrisburg, PA 17105-3608

NAME

VERTICAL HEADER, BLACK,
WITH PEGS, WITH DRAIN HOLES,
VAL-U-LOK(TM)

SIZE
A2

CAGE CODE
00779

DRAWING NO
C-2029134

RESTRICTED TO
-

CUSTOMER DRAWING

SCALE
10:1

SHEET
1 OF 1

REV
A