

May not be suitable for all medical and aerospace applications.

Specifications: Contact Mallory Sonalert to discuss your application.

Resonant Frequency (Hz)	400 ± 100
Operating Voltage (Vdc)	1.5 ~ 2.0
Rated Voltage (Vdc)	1.5
Current Consumption Max. (mA)	30 at Rated Voltage
Sound Pressure Level Min. (dB)	75 at 30cm at Rated Voltage
Tone/Pulse Rate	Constant
Operating Temperature (°C)	-20 ~ +70
Storage Temperature (°C)	-30 ~ +85
Housing	ABS 707 UL94HB plastic resin (Color: Black)
Leading Wire	26 AWG
Weight (Grams)	8.0
Options	For other options contact factory

Dimensions: (units: mm)

RoHS Compliant

