




PART NO.	PANEL THKNS. RANGE	HOLE DIAMETER	"A" REF.	MAX HOLDING BUNDLE DIA. "B"	"C"	PACKAGE
PGSA-0407A	.016-.039 (0.4-1.0)	.272±.004 (6.9±0.1)	.39 (9.8)	.19 (4.8)	.20 (5.0)	1000
PGSA-1013A	.039-.059 (1.0-1.5)	.512±.004 (13±0.1)	.61 (15.5)	.38 (9.6)	.21 (5.4)	500
PGSA-1316A	.039-.055 (1.0-1.4)	.630±.004 (16±0.1)	.72 (18.4)	.49 (12.5)	.21 (5.4)	
PGSA-1519A	.039-.059 (1.0-1.5)	.748±.004 (19±0.1)	.86 (21.8)	.59 (14.9)	.22 (5.7)	
PGSA-1822A	.031-.063 (0.8-1.6)	.866±.004 (22±0.1)	.97 (24.6)	.69 (17.6)	.22 (5.6)	
PGSA-2024A1	.031-.039 (0.8-1.0)	.945±.004 (24±0.1)	1.02 (26.0)	.79 (20.0)	.21 (5.4)	
PGSA-2024A	.039-.047 (1.0-1.2)		1.02 (26.0)	.79 (20.0)	.21 (5.3)	
PGSA-2327A	.016-.039 (0.4-1.0)	1.063-1.071 (27.0-27.2)	1.20 (30.6)	.91 (23.0)	.24 (6.0)	200
PGSA-2529A	.016-.043 (0.4-1.1)	1.142±.004 (29±0.1)	1.28 (32.6)	.98 (25.0)	.28 (7.0)	200



NOTES:

1. MATERIAL: NYLON 6/6 UL 94 V-2 (RMS-01).
NYLON 6/6 UL 94 V-0 (RMS-19),
AVAILABLE BY SPECIAL ORDER. TO ORDER ADD
"-V0" TO THE PART NO.
2. COLOR: BLACK.

TITLE: OPEN/CLOSED BUSHINGS [A SERIES]					DWG IN IN (MM)	
E	SEE CO 200331 FOR CHANGES	SK 02.24.09	FILE # PGSA		DWN: P.B.	APP:
D	SEE CO 200208 FOR CHANGES	SK 06.30.08	MAT'L: SEE NOTES		DT: 07-18-95	DT:
C	SEE ECN #686 FOR CHANGES	SM 08.18.03	RE: RICHCO, INC.		RICHCO INC.	
B	SEE ECN #642 FOR CHANGES	SM 06.11.03			PO BOX 804238, CHICAGO, 60680	
A	CHANGED FILE NO. AND TITLE BLOCK	SM 08.21.02			(773) 539-4060	
REV	DESCRIPTION	ENGR DATE			PART # SEE TABLE	
					PRINT TYPE CA	

TOLERANCES
UNLESS NOTED
.XX=±.010
.XXX=±.005
FRAC=±1/64
ANG=±1°