





THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN H. MOLL CHK T. CLARK APVD T. CLARK		130CTB7 200CTB7 200CTB7		 TE Connectivity	
DIMENSIONS: INCHES 		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± — 1 PLC ± — 2 PLC ± — 3 PLC ± .005 4 PLC ± — ± — ANGLES		NAME HEADER ASSY, MOD II, BREAKAWAY, DOUBLE ROW, .100X.100 ⌀, VERTICAL, WITH .025 SQ POSTS		SIZE CAGE CODE DRAWING NO RESTRICTED TO	
MATERIAL HOUSING: FLAME RETARDANT THERMOPLASTIC; COLOR-BLACK POST: COPPER ALLOY		FINISH POST: .000015 GOLD ON CONTACT .000100— .000250 WHITE TIN-LEAD ON SOLDER TAIL ALL OVER .000050 NICKEL		WEIGHT — A2 00779 C-103186		SCALE 4:1 SHEET 1 of 1 REV J1	
CUSTOMER DRAWING							