



MICRO SWITCH

A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR COMPANY
FREDERICK, ILLINOIS
FED. MFR. CODE 91929ASSEMBLY-
TOGGLE SWITCHCATALOG LISTING
17AT6

(2) 6-32 NC (LOCKING TYPE NUT)

4-40 NC X .125^{REF} ROUND HEAD TERMINAL
SCREWS AND LOCKWASHERS

NOTE-

- 1-UNIT INCLUDES (6) CAT. LIST. V3-201 BASIC SWITCHES
2-SWITCHES DO NOT OPERATE SIMULTANEOUSLY
3-BASIC SWITCH NUMBER INK STAMPED ON EACH BASIC SWITCH AND COVERED WITH CLEAR LACQUER

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CHARACTERISTICS

ELECTRICAL DATA

SCALE-FULL

CONTACT ARRANGEMENT
(6) S. P. D.T.BREAK DISTANCE
.040 APPROX.

DO NOT SCALE PRINT

©

15 A-1/3 HP-125 OR 250 VAC
1/2 A-125 VDC 1/4 A-250 VDC

UNLESS OTHERWISE
SPECIFIED
DIMENSIONS ARE IN INCHES
TOLERANCES ARE:
ONE PLACE (.0) ±.030
TWO PLACE (.00) ±.015
THREE PLACE (.000) ±.005
ANGLES 2

WEIGHT 6.5 OZ MAX

17AT6

M

DRAWING
NUMBER

X 8

X X

ISSUE

X X

REPLACES

RELEASE NO. SR11208

CHECK

REVISIONS

A CO16594

DWV

29 DEC '61

B SR11208

L E B

19 AUG 63

C CO20456

R E R

6 SEP 65

D CO26274

D L F

25 AUG 69

E CO-58771

CHECK

12 FEB 86

F CO 59602

KAG

8 AUG 86

G CO

74352

G R T

17 JAN 94

CHECK

61

DRAWN

K L B

24

AUG

61

PC-80378.003