




Typical Specifications :
1. Rating : DC 12V 50mA
2. Operating Force : 160±50gf
3. Life:300,000 Cycles Min.

NO.2—NO.3	
PART NO	NOTE
01~99	SERIAL NUMBER

⑤	Knob	—	1	PET	Black	—
④	Dust cover	—	1	KAPTON FILM	Yellow	—
③	Terminal	—	2	Phosphor Bronze	Plating silver	—
②	Contact	—	2	F.Ag/SUS	Plating silver	—
①	Base	—	1	Nylon	Black	—
ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK

APPROVALS			DATE				
DRAWN	LIUCAN	2024.7.1					
CHECKED					TITLE:	TACT SWITCHS	
APPROVALS					PART NO.	K2-1837FQ-C3DW-□□	
TOLERANCES ARE			30~以上	±0.30	ANGLE	UNIT: mm	SCALE: 1:1
			10~30	±0.20			
			5~10	±0.15			
			~ 5	±0.10			
			±2'	DRAWING NO.		_____	
					SHEET		1 OF 1

	A		NEW			
ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.