




- NOTES:
- ELECTRICAL CHARACTERS:
 - 1-1.RATING: DC 24V 0.5A;
 - 1-2.CONTACT RESISTANCE:≤30mΩ;
 - 1-3.INSULATION RESISTANCE:≥500MΩ DC 500V;
 - 1-4.WITHSTANDING VOLTAGE:AC 500V 1min;
 - 1-5.LIFE:500 CYCLES;
 - MECHANICAL CHARACTERISTICS:
 - 2-1.INSERTION&EXTRACTION FORCE:3~30N;
 - 2-2.OPERATING TEMPERATURE: -25°C~+70°C;



PCB HOLES(TOP VIEW)

GENERAL TOLERANCE:±0.05mm

4	PIN	1	COPPER ALLOY	Tin plating	T=0.3
3	FRAME	1	Tinplate	—	T=0.3
2	HOUSING	1	PPA	—	BROWN
1	Thread head	1	Zinc alloy	Nickel plating	
NO.	PART NAME	QTY	MATERIAL:	PLATING	REMARK

深圳市富港科技有限公司

TOLERANCE UNLESS OTHERWISE SPEC		TITLE:RF JACK			
BASIC DIMENSION	TOLERANCE	DSND	Z	D	PART NO:IF-1818B-3.5-17.0
x.x	±0.50	CHKD	L	P	J
x.xx	±0.30	APVD	L	Z	W
x.xxx	±0.10				
ANGLES	±3°				



UNIT:mm

SCALE:1:1

SIZE:A4

SHEET:1/1