






REV.	ECN NO.	DATE	SGN	DESCRIPTION
B	LE3-780101	2007/08/09	Cloud	Change 1-adaptor structure and IP level.
C	LEN-7B0210	2007/11/27	Zhong Qin	Change Dimension.
D	LE3-910074	2009/01/14	Vicky	Modify the Wire Harness & Change Dimension



Conn.2&3

Pin Assignments

Front View




Conn.1

Pin Assignments

Front View

Blue (24AWG)	藍	5	5	5
White (24AWG)	白	4	4	4
Black (22AWG)	黑	3	3	3
Red (22AWG)	紅	2	2	2
Green (24AWG)	綠	1	1	1
Wire Color		Conn.1	Conn.2	Conn.3

Pin Out



M12.0*1.0



Note:

- * Important Dimension.
- * Waterproof Rate:IP68.
- * In 1 meter water within 24 hours.
- * Connector:Black,PU.
- * O-Ring:Green,Viton.
- * Screw Nut:Zinc Alloy,Nickel Plated.
- * Pin:Copper Alloy,Gold Plated.
- * Wire Harness:UL1061 24AWG, Green,White,Blue.
- * Wire Harness:UL1061 22AWG, Red,Black.

UNIT:mm

TOLERANCE

±0.5 mm

TITLE M12 Conn T Adaptor

FMM Conn FMM Pin,5Pin

SCALE	SIZE	SHEET	OF	1
REV. D	A4	@@	Inspection	Item

Amphenol LTW

安費諾亮泰企業股份有限公司

ITEM NO SS-050505-FMM-TS001

DWG NO

SS-050505-FMM-TS001

CUSTOMER ALTW

DRAWN BY Vicky

CHECKED BY

Ivan

APPROVED BY Luke

DATE 2009/01/14

DATE 2009/01/14

DATE 2009/01/14