







THIS DRAWING IS UNPUBLISHED.
RELEASED FOR PUBLICATION
20
COPYRIGHT 20 BY Tyco Electronics Japan G.K. ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN APVD
J	-			SEE SHEET 1 OF 3		







推奨基板取付穴寸法: コネクタ搭載面 (非累積公差)
PC基板厚: $1.0 \sim 1.6 \pm 0.1$
RECOMMEND PC BOARD HOLE PATTERN
: CONNECTOR MOUNT SIDE (NOT ACCUMULATE TOLERANCE)
PC BOARD THICKNESS : $1.0 \sim 1.6 \pm 0.1$

ONLY 4POS



4POS(X-KEY):1-1827875-2

SCALE 2:1












6POS(X-KEY):1-1827875-3

8POS(X-KEY):1-1827875-4

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	T. KUDO	14JAN2005	 TE Connectivity	
		CHK	D. MITSUGI	14JAN2005		
DIMENSIONS:		APVD	D. MITSUGI	14JAN2005	NAME	
mm		PRODUCT SPEC	108-78268			
		APPLICATION SPEC	114-5377		DYNAMIC DI200D 2.5mmPITCH HDR ASSY (V-TYPE) 4-20POS	
		WEIGHT	-			
MATERIAL		FINISH	-		SIZE	CAGE CODE
					A3	00779
					DRAWING NO	C-1827875
					RESTRICTED TO	-
					SCALE	4:1
					SHEET	2 OF 3
					REV	B



LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	APVD
J	-			SEE SHEET 1 OF 3		



10POS(X-KEY):1-1827875-5

12POS(X-KEY):1-1827875-6

16POS(X-KEY):1-1827875-8

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN T. KUDO	14JAN2005	 TE Connectivity				
DIMENSIONS: mm		CHK D. MITSUGI	14JAN2005					
		APVD D. MITSUGI	14JAN2005	NAME DYNAMIC DI200D 2.5mmPITCH HDR ASSY (V-TYPE) 4-20POS				
		PRODUCT SPEC 108-78268						
		APPLICATION SPEC 114-5377		SIZE A3		CAGE CODE 00779	DRAWING NO C-1827875	RESTRICTED TO -
		WEIGHT -						
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±0.5 2 PLC ±0.13 3 PLC ±0.013 4 PLC ±0.0001 ANGLES ±0.0001		CUSTOMER DRAWING		SCALE 4:1		SHEET 3 OF 3		REV B
MATERIAL &material		FINISH -						