

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

, 19

© COPYRIGHT 19


BY AMP INCORPORATED. ALL INTERNATIONAL RIGHTS RESERVED.

LOC	DIST	P	F	REVISIONS				
				ZONE	LTR	DESCRIPTION	DATE	APPD
G	14				C	REV PER 063A-0435-02	30SEP02	JR MS

METRIC

DIMENSIONS LISTED IN mm [INCHES]

AMP WIRE RANGE	 E13288 Listed
500-600 MCM STRANDED	500-600 MCM STRANDED
 LR7189 Certified	MILITARY P/N AND CLASS
500-600 MCM STRANDED	NOT APPLICABLE



- 1
- 2
- 3
- STAMP AMP W* 500-600 MCM APPROX AS SHOWN
- MATERIAL THK: 4.52^{±0.10} [.178^{±.004}]
- STAMP FOR MANUFACTURING LOCATION OR CODE PERMISSIBLE.

AMP INCORPORATED CUSTOMER SERVICE SYSTEMS			MAX RECOMMENDED OPERATING TEMPERATURE: 170°C MAX					PART NO	
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752		VOLTAGE RATING: NOT APPLICABLE	CIRCULAR MIL AREA: 242.2-304.0mm ² [478-600] MCM STRANDED	DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm [INCHES] TOLERANCES ON: 2 PLC DEC ± 0.20[.008] 3 PLC DEC ± - ANGLES ± -		DR 5/6/93 DK SCHRUM	 AMP Incorporated Harrisburg, PA 17105-3608	
					MATERIAL COPPER PER ASTM B-152 ANNEALED		CHK 5/14/93 AJ KAUFMAN		
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111		THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.	FINISH TIN PLATE 0.00254[.000100] MIN THK PER MIL-T-10727	APPD 5/14/93 RE ROSEY		NAME SPLICE, PARALLEL, SOLISTRAND, WIRE SIZE: 500-600 MCM		
FOR ORDER ENTRY	1-800-526-5142	PRODUCT SPEC -			APPD 5/14/93 CR RHOADS		SIZE B CAGE CODE 00779 DRAWING NO C-322278		
		APPLICATION SPEC -			SCALE 1:1				
		WEIGHT -			SHEET 1 OF 1				