



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	REL PER ECO-18-013881	27AUG2018	JM	RB
	A1	REV PER ECO-18-016694	18OCT2018	JM	RB


D



2320933-2
SCALE 2:1
KEY B




2320933-3
SCALE 2:1
KEY C




2320933-4
SCALE 2:1
KEY D

C




2320933-1 SHOWN
KEY A

B




SECTION A-A

A



SECTION A-A

- 1 MATERIAL: 15% FIBERGLASS REINFORCED PBT
COLOR: GRAY
- 2 MATERIAL: 15% FIBERGLASS REINFORCED PBT
COLOR: (SEE TABLE)
- 3 MATERIAL: SILICONE
COLOR: RUST
- 4 MATERIAL: 15% FIBERGLASS REINFORCED PBT
COLOR: ORANGE
- 5 MATERIAL: SILICONE
COLOR: TAN
6. RECOMMENDED WIRE DIAMETER RANGE IS 1.30 TO 2.54mm.
7. RECOMMENDED BACKSHELLS:
- STRAIGHT EXIT:
- A. 2292798-1 SMOOTH WIRE EXIT
 - B. 2292798-2 NC12/NW10 CONDUIT WIRE EXIT
 - C. 2292798-3 NC08/NW7.5 CONDUIT WIRE EXIT
- 90° EXIT:
- D. 2302491-1 SMOOTH WIRE EXIT
 - E. 2302491-2 NC12/NW10 CONDUIT WIRE EXIT
 - F. 2302491-3 NC08/NW7.5 CONDUIT WIRE EXIT
8. RECOMMENDED SEAL PLUG: 776363-1
9. MATING CONNECTOR: 2320927-X.



SCALE 2:1

D	ORANGE	2320933-4
C	PURPLE	2320933-3
B	BLUE	2320933-2
A	TAN	2320933-1
KEY	TPA COLOR	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J. MCNEAL 07FEB2018	TE Connectivity			
DIMENSIONS: mm		CHK R. BALTER 07FEB2018				
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD R. BALTER 07FEB2018	NAME PLUG ASSEMBLY, 3 POSITION, REDUCED DIA SEAL, HIGH TEMP, AMPSEAL 16			
0 PLC ± 1 PLC ± 2 PLC ±0.30 3 PLC ± 4 PLC ± ANGLES ±1° FINISH		PRODUCT SPEC 108-2184 APPLICATION SPEC 114-13065 WEIGHT 8g	SIZE A2	CAGE CODE -	DRAWING NO C-2320933	RESTRICTED TO -
MATERIAL -		CUSTOMER DRAWING		SCALE 4:1	SHEET OF	REV A1