








REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	LEN1130363	2011/03/11	Kevin Wang	Modify the Dimension
C	LEN1180142	2011/08/27	baowei	Add Wire Size
D	LEN1350170	2013/05/03	Sam	Change Dimension



Pin Screws (4)
Pin Retainers (5)




- 1 Female Housing
- 2 O-ring 1
- 3 Female Pins



Pin Assignments
Front View

M3*0.5 (Non Through Hole)




Recommended
Panel Cut-Out

Note:

- * (QC) Important Dimensions To Check.
- * Waterproof Rate: IP67
- * Female Housing: Nylon+GF, Black
- * Female Pin: Copper Alloy, Gold Plated
- * Pin Screws: 1.5mm(HEX), Stainless Steel
- For wire assembly, tightened by tool.
- * Cond. Retainer: Copper Alloy, Gold Plated
- * O-ring: Silicone, Gray
- * Flame Class: UL94V-0
- (7) * One Set Assembled in one PE Bag
- (C) * 1.5mm Hex Tool for Screws sold separately
- * Wire Size Range: 14AWG~18AWG

UNIT:mm



TOLERANCE

.X ±0.25
.XX ±0.1
.XXX ±0.05
ANGLES ±1°

TITLE
Panel Female Power Conn.16Amp
Screw in Type Pin (Gold Plated)

SCALE
1:1

SIZE
A4

SHEET
1 OF 1

REV.
D

WC-REV.
A.4

(QC): Inspection item

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO. PWG-04PFFB-SC7001	DRAWN BY SamChang	DATE 2013-05-03
DWG NO. PWG-04PFFB-SC7001	CHECKED BY Rita	DATE 2013-05-03
CUSTOMER ALTW	APPROVED BY Maslow	DATE 2013-05-03