


SPECIFICATIONS:

<b>MATERIALS:</b>	
HOUSING:	PBT, UL94 V-0, BLACK
CONTACTS:	GOLD PLATED BRASS (SEE P/N KEY BELOW)
NUT:	NICKEL PLATED BRASS
SHELL:	NICKEL PLATED BRASS
ORING:	EPDM, BLACK




<b>ELECTRICAL:</b>	
RATED CURRENT:	1A
RATED VOLTAGE:	60V
INSULATION RESISTANCE:	100 MOhms MIN.
CONTACT RESISTANCE:	10 mOhms MAX.

<b>ENVIRONMENT:</b>	
OPERATING TEMPERATURE:	-40°C TO +85°C
WATER PROOF:	IP67



853-004-113R00Y

1 = GOLD FLASH  
4 = 10u" GOLD



RoHS COMPLIANT

DRAWN:	M. SIGMON
DATE:	03/04/2016

UNITS = inch [mm]

DO NOT SCALE FROM DRAWING



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

NorComp

SCALE:	NTS	SHEET	1	OF	1	REV	9
DWG NO.	853-004-113R00Y						