

NOTES: UNLESS OTHERWISE SPECIFIED

1. FOR USE WITH RG-405 OR EQUIVALENT CABLE.

2. MATERIAL SPECIFICATIONS:

INSULATOR: PTFE

SPACER: DELIN , COLOR: NATURAL

OUTER CONTACT: BERYLLIUM COPPER

ALL OTHER METAL PARTS: BRASS

3. FINISH SPECIFICATIONS:

CONTACT: .000003 MIN THICK GOLD OVER .000050 MIN THICK NICKEL

ALL OTHER METAL PARTS: THIN GOLD OVER .000050 MIN THICK COPPER

4. ELECTRICAL SPECIFICATIONS:

IMPEDANCE: 50 OHMS


FREQUENCY RANGE: DC TO 6 GHz

VSWR: 1.5 MAX




5. CAP AND SPACER SHIPPED LOOSE.

6. RoHS COMPLIANT.

REV	DESCRIPTION	BY DATE	APPD
A	ERO55647	MS 11/05/14	MS



RECOMMENDED
CABLE STRIPPING DIMS



PER ASME Y14.5M-1994
UNLESS OTHERWISE SPECIFIED:
DIMENSIONS ARE IN INCHES [MM]
TOLERANCES:
DECIMAL: .XX [XX] ± .01 [0.3]
XXX [XXX] ± .005 [0.13]
XXXX [XXXX] ± .0001 [0.0025]
ANGLES: ± 2° SCALE: X:1

CUSTOMER
SALES DRAWING



WINCHESTER Winchester Electronics Corporation
ELECTRONICS 199 Park Road Ext Suite 104
Middlebury, Connecticut 06762

MCX RIGHT ANGLE DIRECT SOLDER
PLUG FOR RG-405CABLE

DRAWN	DATE	APPROVED	DATE
MS	11/05/14	MS	11/05/14
APPROVED	DATE	APPROVED	DATE
XXX	XX/XX/XX	XXX	XX/XX/XX

REV	DESCRIPTION	BY DATE	APPD
A	1213A204-405	MS 11/05/14	MS