



OP-AR50

([Home](#) : [Products](#) : [Switches](#) : [MICRO SWITCH™ Limit Switches](#) : [MICRO SWITCH™ Global Limit Switches](#) : [OP](#))

Image Not Available

Enclosed Switch Series OP: Manually Actuated Palm Switch (3 in x 3.5 in), 1NO 1NC Snap Action SPDT

Actual product appearance may vary.

Product Specifications

Availability	Global
Operating Force (OF)	11,0 N [2.4 lb]
Product Type	Enclosed Switches
Actuator	Manual Palm Button
Circuitry	1NC 1NO Snap Action, SPDT
Ampere Rating	15 A
Supply Voltage	125 Vac, 250 Vac, 480 Vac
Housing Material	Aluminum Die-Cast
Termination Type	0.5 in - 14NPT Conduit
Series Name	OP
Sealing	NEMA 1, 3, 4, 13
UL File #	E12252
Comment	Large 3.0 in x 3.5 in paddle for fast, easy operation.
Agency Approvals and Standards	UL, CSA
UNSPSC Code	39122213
UNSPSC Commodity	39122213 Limit Switches