

INTERCONNECTS

SERIES 321, 322, 323, 324 • 2,54 GRID WRAPOST • SINGLE ROW STRIPS




FIG. 1




FIG. 2




FIG. 3




FIG. 4

- Wraposts available in 1 - 4 levels using MM pin numbers:

1-Level uses pin # 0040-1

2-Level uses pin # 0089-2


3-Level uses pin # 0088-3

4-Level uses pin # 0086-4

See page 198 for details

- Hi-Rel, 4-finger BeCu #30 contact is rated at 3 amps. See page 253 for details

- Insulators are high temperature thermoplastic, suitable for all soldering operations



ORDERING INFORMATION

FIG. 1	Series 321...001	1 Level Wrapost
	321-13-1	-41-001000 Specify number of pins 01-64
FIG. 2	Series 322...001	2 Level Wrapost
	322-XX-1	-41-001000 Specify number of pins 01-64
FIG. 3	Series 323...001	3 Level Wrapost
	323-XX-1	-41-001000 Specify number of pins 01-64
FIG. 4	Series 324...002	4 Level Wrapost
	324-XX-1	-41-002000 Specify number of pins 01-64



XX=Plating Code
See Below

For
Electrical, Mechanical
& Environmental Data,
See page 264

SPECIFY PLATING CODE XX=	11	13	91	93	41	43	
Sleeve (Pin)	0,25µm Au	0,25µm Au	5,08µm Sn/Pb	5,08µm Sn/Pb	5,08µm Sn	5,08µm Sn	
Contact (Clip)	0,25µm Au	0,76µm Au	0,25µm Au	0,76µm Au	0,25µm Au	0,76µm Au	

